

The air-cooled MIG/MAG welding torches meet the needs of welders for a wide range of welding tasks.

DESCRIPTION

Light and handy torch.
For car bodywork and fine sheet metal work.
Economical and safe solution.
Small footprint.

FEATURES

- **Max current (I_{max}):** 180 A: CO₂ and 150 A: Ar/CO₂
In pulsed mode, these capacities are reduced by 35%.
- **Duty cycle :** 150 A @ 60 %.
- **Recommended wire diameters:** 0.6 to 1.0 mm
- **Length:** 3 m



CONSUMABLES

Torch



Contact tube supports & diffusers



Contact tubes

	STEEL	ALU
Ø 0.6	041905	-
Ø 0.8	041912 ●	041059 ●
Ø 1.0	041929	041066
Ø 1.2	040144	041073

Nozzles

A		welding
B		pointing
C		soda nail
D		no gas
	ACIER	ALU
A	041875 ●	041875 (Ø 12) ● 046214 (Ø 16)
B	041851	041851
C	041523	-
D	041868	-

Sheath

	Ø 0.6/0.8		Ø 1.0 & 1.2	
	3 m	4 m	3 m	4 m
Steel	041592 ●	041837	041608	041844
Teflon	041578 ●	044050	041585	044067
Carbon	-	039834	-	039827

Consumables box option:

	x3
	x5
	x5 (M6-Ø 0.6)
	x5 (M6-Ø 0.8)
	x5 (Alu-M6-Ø 0.8)
	x3



- Original steel equipment
- Original aluminium equipment