

Technical specification

Technology & bands	<ul style="list-style-type: none">o GSM / 2Go 2G Dual Carrier	900 / 1900 MHz Yes
Ringtone volume	<ul style="list-style-type: none">o 72 dB(A) at a distance of 30 cm	
Connectivity	<ul style="list-style-type: none">o USB data porto USB versiono Bluetooth®o Bluetooth® version	Yes 1.1 Yes 2.1 + EDR
SIM	<ul style="list-style-type: none">o Dual SIMo SIM1o SIM2	Yes mini SIM mini SIM
Memory	<ul style="list-style-type: none">o ROM + RAMo External memoryo Max. capacity	32 MB + 32 MB Memory card 32 GB
Charger	<ul style="list-style-type: none">o Inputo Output	100 – 240 V ~ 50/60 HZ 0,25 A 5,0 V – 500 mA
Battery	<ul style="list-style-type: none">o Type:o Capacityo Standby:o Talk timeo Multimedia:	Lithium-ion 800 mAh up to 550 hours up to 10 hours up to 8 hours
Dimensions & Weights	<ul style="list-style-type: none">o Dimensions:o Weight:	109,4 x 58,0 x 18,8 mm (closed) 206,0 x 58,0 x 12,0 mm (open) (H x W x D) 113 g incl. battery 93 g without battery
Scope of supply	<ul style="list-style-type: none">o Gigaset GL590 blacko Chargero Charging cableo Batteryo Quick-start-guideo Headset (only FR)o Headset connector (only FR)	
Appliance colour	<ul style="list-style-type: none">o Black	
Datasheet version		14.08.2023