

Item no.: 3028087, 3028088, 3028089, 3028090, 3028091, 3028092, 3028093

Data Sheet

LiFY PVC-stranded wires set

BN	3028087	3028088	3028089	3028090	3028091	3028092	3028093
Nominal Voltage	Below 75V/ DC or 50V/ AC						
Test Voltage	1.5KV						
Cross section	0.14mm ²	0.25 mm ²	0.34 mm ²	0.5 mm ²	0.75 mm ²	1.0 mm ²	1.5 mm ²
External diameter	Ø1.3mm	Ø1.4mm	Ø1.6mm	Ø2.0mm	Ø2.2mm	Ø2.5mm	Ø2.7mm
No. of conductor	28	50	17	100	96	32	85
Conductor diameter	0.08mm	0.08mm	0.16mm	0.08mm	0.1mm	0.2mm	0.15mm
Color	Black, White, Red, Blue, Brown, Grey, Yellow-Green (7 colors)						
Cable length	10 meter each color	10 meter each color	5 meter each color	5 meter each color	5 meter each color	5 meter each color	5 meter each color
Insulation material	PVC						
Conductor material	Bare copper						
Temperature range	-15°C~+80°C						