

SAMSUNG



Crystal UHD Signage

QHC Series

Slim design. Stunning performance.

Introducing the QHC series, the slimmest display in the Samsung's UHD signage offerings. This products deliver an unparalleled slim design that fits into any business, while delivering the visual quality to make a big impact. The sleek form factor is easily installed to fit any room design and delivers stunning visual performance. Dynamic Crystal Color and Quantum Processor Lite 4K delivering consistent, lifelike colors to any content. This is not just a display for simple advertising. It's a display that brings the solutions, tools, and picture quality to grow to your business, no matter what industry you're in.

Key features



Ultra Slim Depth

The unparalleled ultra-slim thickness of 28.5mm makes it the thinnest option in Samsung's UHD Signage series. It comes with the Slim Fit Wall Mount, which allows you to install it neatly and easily in any environment.



Even Bezels and Centered VESA Holes

The bezels are even on all four sides of the display for a consistent look, while the central VESA mounting holes ensure secure mounting and easy adjustability to portrait mode.



Dynamic Crystal Color

One billion shades of color let you see every subtlety with lifelike color variations. Images are clear and consistent thanks to Samsung's industry leading video processing and upscaling technology.



Smartview+

In the QHC series, SmartView+ enables wireless screen sharing for easy collaboration and quick screen switching with just a click.



Smart Calibration

Guarantee complete brand consistency across every location. Using the Samsung mobile app, calibrate displays to showcase brand logos and other collateral in the exact colors required.



Energy star / EPEAT Bronze

Samsung is making diverse efforts to reduce our environmental impact in smart signage, and encouraging users to pursue a more sustainable life.

Specifications

Model			QH43C	QH50C	QH55C	QH65C	QH75C	
Display Panel	Diagonal Size	Class	43	50	55	65	75	
		Measured	42.5	48.5	54.6	64.5	74.5	
	Resolution		3,840 x 2,160 (16:9)	3,840 x 2,160 (16:9)	3,840 x 2,160 (16:9)	3,840 x 2,160 (16:9)	3,840 x 2,160 (16:9)	
	Brightness (Typ.)		700 nit	700 nit	700 nit	700 nit	700 nit	
	Orientation		Landscape/Portrait	Landscape/Portrait	Landscape/Portrait	Landscape/Portrait	Landscape/Portrait	
	Haze		25%	25%	25%	25%	25%	
	Contrast Ratio (Typ.)		4,000:1	4,000:1	4,000:1	4,000:1	4,000:1	
	Type		VA	VA	VA	VA	VA	
	Active Display Area		941.184 (H) x 529.416 (V)	1,095.84 (H) x 616.41 (V)	1,209.6 (H) x 680.4 (V)	1,428.48 (H) x 803.52 (V)	1,650.24 (H) x 928.26 (V)	
	Pixel Pitch (mm)		0.245 x 0.245	0.285 x 0.285	0.315 x 0.315	0.372 x 0.372	0.429 x 0.429	
Color Gamut		NTSC 72%	NTSC 72%	NTSC 72%	NTSC 72%	NTSC 72%		
Operation Hour		24/7	24/7	24/7	24/7	24/7		
Connectivity / Sound	Input	Video	DP1.2 (1), HDMI 2.0 (3)	DP1.2 (1), HDMI 2.0 (3)	DP1.2 (1), HDMI 2.0 (3)	DP1.2 (1), HDMI 2.0 (3)	DP1.2 (1), HDMI 2.0 (3)	
		Audio	N/A	N/A	N/A	N/A	N/A	
		USB	USB 2.0 x 2	USB 2.0 x 2	USB 2.0 x 2	USB 2.0 x 2	USB 2.0 x 2	
		Tuner	N/A	N/A	N/A	N/A	N/A	
	Output	Video	N/A	N/A	N/A	N/A	N/A	
		Audio	Stereo mini Jack	Stereo mini Jack	Stereo mini Jack	Stereo mini Jack	Stereo mini Jack	
		USB	N/A	N/A	N/A	N/A	N/A	
	WiFi / BT		O/O	O/O	O/O	O/O	O/O	
	External Control		RS232C (In/Out), RJ45	RS232C (In/Out), RJ45	RS232C (In/Out), RJ45	RS232C (In/Out), RJ45	RS232C (In/Out), RJ45	
	Speaker		10W 2ch	10W 2ch	10W 2ch	10W 2ch	10W 2ch	
Mechanical Spec	Dimension (mm / in.)	Set	969.5 x 557.8 x 28.5 mm / 38.2 x 22 x 1.1 in.	1,124.1 x 644.8 x 28.5 mm / 44.3 x 25.4 x 1.1 in.	1,237.9 x 708.8 x 28.5 mm / 48.7 x 27.9 x 1.1 in.	1,456.8 x 831.9 x 28.5 mm / 57.4 x 32.8 x 1.1 in.	1,682.3 x 960.4 x 28.5 mm / 66.2 x 37.8 x 1.1 in.	
		Package	1,093 x 667 x 126 mm / 43 x 26.3 x 5 in.	1,246 x 761 x 131 mm / 49 x 30 x 5.2 in.	1,403 x 835 x 148 mm / 55.2 x 32.9 x 5.8 in.	1,616 x 945 x 164 mm / 63.6 x 37.2 x 6.5 in.	1,839 x 1,113 x 180 mm / 72.4 x 43.8 x 7 in.	
	Weight (kg / lbs.)	Set	9.3 kg / 20.5 lbs.	12.4 kg / 27.3 lbs.	16.9 kg / 37.3 lbs.	22.4 kg / 49.4 lbs.	34.2 kg / 75.4 lbs.	
		Package	11.8 kg / 26 lbs.	15.5 kg / 34.2 lbs.	21.1 kg / 46.5 lbs.	29.8 kg / 65.7 lbs.	44 kg / 97 lbs.	
	VESA Mount		200 x 200	200 x 200	200 x 200	200 x 200	200 x 200	
	VESA Mount Screw (Min-Max)		M8, 12-14mm	M8, 12-14mm	M8, 12-14mm	M8, 12-14mm	M8, 12-14mm	
	Bezel Width (mm)		11.5 (Even)	11.5 (Even)	11.5 (Even)	11.5 (Even)	13.4 (Even)	
Features	Key		UHD Signage with Built-in MagicInfo S10, SSSP10.0	UHD Signage with Built-in MagicInfo S10, SSSP10.0	UHD Signage with Built-in MagicInfo S10, SSSP10.0	UHD Signage with Built-in MagicInfo S10, SSSP10.0	UHD Signage with Built-in MagicInfo S10, SSSP10.0	
	Operating System		Tizen 7.0	Tizen 7.0	Tizen 7.0	Tizen 7.0	Tizen 7.0	
	Internal Player	Processor	CA73 1.6GHz Quad-Core	CA73 1.6GHz Quad-Core	CA73 1.6GHz Quad-Core	CA73 1.6GHz Quad-Core	CA73 1.6GHz Quad-Core	
		Storage (FDM)	16GB (10GB available)	16GB (10GB available)	16GB (10GB available)	16GB (10GB available)	16GB (10GB available)	
	H/W		2nd Gen. B2B Design Center IR Temperature Sensor Ambient Sensor Auto Level	2nd Gen. B2B Design Center IR Temperature Sensor Ambient Sensor Auto Level	2nd Gen. B2B Design Center IR Temperature Sensor Ambient Sensor Auto Level	2nd Gen. B2B Design Center IR Temperature Sensor Ambient Sensor Auto Level	2nd Gen. B2B Design Center IR Temperature Sensor Ambient Sensor Auto Level	
	Special	S/W	Wi-Fi(2.4/5.0GHz dual) and BT Signage New Home Workspace (Microsoft377/VMWare/RDP) Custom Home Auto Source Switching and Recovery Dicom Simulation Mode Director Mode SmartView+ Upgradable Web-Engine Tizen Enterprise Platform Video Conference Solution Smart Calibration	Wi-Fi(2.4/5.0GHz dual) and BT Signage New Home Workspace (Microsoft377/VMWare/RDP) Custom Home Auto Source Switching and Recovery Dicom Simulation Mode Director Mode SmartView+ Upgradable Web-Engine Tizen Enterprise Platform Video Conference Solution Smart Calibration	Wi-Fi(2.4/5.0GHz dual) and BT Signage New Home Workspace (Microsoft377/VMWare/RDP) Custom Home Auto Source Switching and Recovery Dicom Simulation Mode Director Mode SmartView+ Upgradable Web-Engine Tizen Enterprise Platform Video Conference Solution Smart Calibration	Wi-Fi(2.4/5.0GHz dual) and BT Signage New Home Workspace (Microsoft377/VMWare/RDP) Custom Home Auto Source Switching and Recovery Dicom Simulation Mode Director Mode SmartView+ Upgradable Web-Engine Tizen Enterprise Platform Video Conference Solution Smart Calibration	Wi-Fi(2.4/5.0GHz dual) and BT Signage New Home Workspace (Microsoft377/VMWare/RDP) Custom Home Auto Source Switching and Recovery Dicom Simulation Mode Director Mode SmartView+ Upgradable Web-Engine Tizen Enterprise Platform Video Conference Solution Smart Calibration	
		Safety		60950-1/62368-1	60950-1/62368-1	60950-1/62368-1	60950-1/62368-1	60950-1/62368-1
	Certification	EMC		Class B	Class B	Class B	Class B	Class B
		Environment		ENERGY STAR 8.0, EPEAT	ENERGY STAR 8.0, EPEAT	ENERGY STAR 8.0, EPEAT	ENERGY STAR 8.0, EPEAT	ENERGY STAR 8.0, EPEAT
		IP Rating		IP5x	IP5x	IP5x	IP5x	IP5x
Security		802.1x (WPA2 Enterprise): EAP-TLS, EAP-TTLS, EAP-PEAP	802.1x (WPA2 Enterprise): EAP-TLS, EAP-TTLS, EAP-PEAP	802.1x (WPA2 Enterprise): EAP-TLS, EAP-TTLS, EAP-PEAP	802.1x (WPA2 Enterprise): EAP-TLS, EAP-TTLS, EAP-PEAP	802.1x (WPA2 Enterprise): EAP-TLS, EAP-TTLS, EAP-PEAP		
Power	Power Supply		AC 100 - 240 V, 50/60 Hz	AC 100 - 240 V, 50/60 Hz	AC 100 - 240 V, 50/60 Hz	AC 100 - 240 V, 50/60 Hz	AC 100 - 240 V, 50/60 Hz	
	Power Consumption	Max [W/h]	TBD	TBD	TBD	TBD	TBD	
		Typical [W/h]	TBD	TBD	TBD	TBD	TBD	
Sleep mode		less than 0.5W	less than 0.5W	less than 0.5W	less than 0.5W	less than 0.5W		
Operating Condition	Temperature		0°C - 40°C	0°C - 40°C	0°C - 40°C	0°C - 40°C	0°C - 40°C	
	Relative Humidity		10-80%	10-80%	10-80%	10-80%	10-80%	
Accessories	Included		Quick Setup Guide, Warranty Card, Power Cord RS232C (In) Gender Remote Controller and Batteries	Quick Setup Guide, Warranty Card, Power Cord RS232C (In) Gender Remote Controller and Batteries	Quick Setup Guide, Warranty Card, Power Cord RS232C (In) Gender Remote Controller and Batteries	Quick Setup Guide, Warranty Card, Power Cord RS232C (In) Gender Remote Controller and Batteries	Quick Setup Guide, Warranty Card, Power Cord RS232C (In) Gender Remote Controller and Batteries	
	Optional	Stand	STN-L4355C	STN-L4355C	STN-L4355C	STN-L6585C	STN-L6585C	
		Mount	WMN-B505C	WMN-B505C	WMN-B505C	WMN-B505C	WMN-B505C	
		Specialty	TBD	TBD	TBD	TBD	TBD	

Learn More samsung.com/display samsung.com/business insights.samsung.com
 Product Support 1-866-SAM4BIZ
 Follow Us youtube.com/samsungbizusa [@SamsungBizUSA](https://twitter.com/SamsungBizUSA)

