

Data sheet

Article Description

Article Picture

USB Socket Combination 2-fold Type 9016

horizontal, Socket outlet with earthing contact and USB charger, socket with increased contact protection, ready for use with insulating socket, black cable 3 x 1.5 mm², length 2 m with angle plug earthing contact/Belgium-France



Dimensions: LWH 113 x 60 x 49 mm
 Small installation depth: 41 mm
 Installation diameter: 50 mm
 Protection class: IP20, for dry rooms only

Socket: max. load 250 V
 16 A - 3.5 KW



USB Charger:

Input: 100 – 240 V AC
 Output: 5 – 12 V DC, 20 W max.
 Performance:

	<u>5,0 V</u>	<u>9,0 V</u>	<u>12,0 V</u>
1 x USB A Quick Charge 3.0	3,0 A	2,22 A	1,67 A
1 x USB C Power Delivery 3.0	3,0 A	2,22 A	1,67 A

C + A Output: 5.0 V, 3,0 A – 15 W max.
 Stand-by: 0.3 W

Ideal for vertical installation in front of example

- beside tables
- desks
- furniture
- kitchen

Plug & Play



Not suitable for flush-mounted wall installation, installation on worktops and use in damp rooms and outdoor areas.

The place of installation has to be chosen according to the installation instructions.

<i>inter BÄR-No.</i>	<i>Colour</i>
9016-114...	black
9016-118...	white

Technical modifications reserved!