


CRYSTAL WUV







• 150

MAX LUMENS

METERS THROW

(3)

DAYS RUNTIME

50/62

WHITE. ULTRAVIOLET LIGHT

•

RECHARGEABLE

Built-in battery charges with any Micro USB cable



DIMENSIONS

Length 63 mm Width 43 mm Height 15 mm Weight 34 g




Compact multi flashlight with white and ultraviolet light

Crystal WUV is a universal model of the Crystal series with white and ultraviolet light. Just like other Armytek compact multi flashlights, Crystal WUV provides a wide flood light for use at close range during an evening walk, jogging or performing tasks in low-light conditions. However, thanks to an additional LED, the capabilities of the flashlight are significantly expanded. UV light allows reading hidden inscriptions and marks, as well as detecting leaks of technical liquids and household stains.

Weighing only 34 grams, the compact multi flashlight is convenient to carry in a pocket or bag together with keys. It can also be fixed on the head with the headband or attached to clothes, belt or a backpack strap with a clip. In addition to that, the set includes a convenient lanyard for wearing on a wrist or around the neck. With the durable lanyard, Crystal WUV can be hung on a branch of the nearest tree or on a hook under the ceiling of a tent to illuminate the campsite during a trip to nature.

ARMYTEK CRYSTAL WUV REV_0000





3 KEYCHAIN LIGHTWear-resistant plastic rings for keys or lanyard.



Body made from durable materials, constant

light without flickering. Multiple variants of

4 SPORTS FLASHLIGHT

installation on sporting gear.

1 HEADLAMP
Soft elastic headband. Special design with thought-out optical elements provides convenient beam angle of white light with minimum loss of light for use at a close distance.



2 EVERY DAY CARRY LIGHT

Lightweight and compact body. Possibility to attach to bag, pocket, shoulder strap or cap using a clip. Paracord lanyard for wearing on a wrist or around the neck.



5 LAMP MODEWorks directly from a Powerbank or any USB power supply.

ARMYTEK CRYSTAL WUV REV_0000



6 SIGNAL LIGHT Different operating modes, omnidirectional light.



• Convenient operation with one button, double click to change the type of light

Unique fully luminous body



• Built-in Li-Pol 600 mAh battery charges with any Micro USB cable

· Color indication of charging process


 IP67 standard: reliable protection from dust and submersion at 1 meter for 30 minutes.
 Withstands fallings from up to 10 meters



Ultraviolet light with 365 nm wavelength is for verification of currency and passports authenticity, revealing household stains, detecting leaks



ARMYTEK CRYSTAL WUV REV_0000







SET DESCRIPTION

- 1 flashlight with built-in battery
- **2** headband
- 3 lanyard
- **4** user manual in eight languages









SPECIFICATIONS

		Crystal WUV		
		White light	Ultraviolet light	
Light output		150 lm	325 mW	
Beam distance		12 m	-	
Hotspot: Spill		70° : 140°		
Brightness stabilization type		Digital		
Number of modes		5	5	
Modes / Runtimes	Main3 Main2 Main1 Firefly Beacon	150 lm / 2 h 15 min 36 lm / 8 h 10 min 5 lm / 54 h 0.1 lm / 50 d 150 lm / 1 Hz / 9 h 50 min	325 mW / 6 h 52 min 100 mW / 9 h 43 min 15 mW / 52 h 1 mW / 62 d 325 mW / 1 Hz / 34 h	
Power source (built-in)		Li-Pol 600 mAh		
Length / width / height (without clip)		63 mm / 43 mm / 15 mm		
Weight		34 g		
Ingress protection, Submersion and Impact resistance		IP67. Depth up to 1 m for 30 min. Height up to 10 m		

▶ All the above specifications are test results based on ANSI/PLATO FL 1-2019 Standard. The data may vary due to environment, heat dissipation and other factors.

ARMYTEK CRYSTAL WUV REV_0000

BENEFITS OF WORKING WITH ARMYTEK

Armytek is a world famous manufacturer of high-tech flashlights, chargers and accessories. All Armytek products perfectly meet the buyer's requirements. We focus on quality and reliability: smart lineup allows us to thoroughly think through every detail before launching mass production.

HIGH PROFIT

Favorable conditions and flexible prices for bulk orders are ensured by own factories in China.



★ FAST SHIPPING

Warehouses around the world: the goods are always in stock and ready for shipment. Reduced costs and time of delivery, no additional customs fees required. Lower costs on shippings directly from the factories.



EXCEPTIONAL RELIABILITY

Minimum returns rate - less than 1% (competitors' rate is 5-7%). All products go through quality checking on test stands.



* LEGENDARY SERVICE

Full support and cooperation: from placing an order to warranty service. Professional issue management, fast repairs and exchange.



NO HASSLE WARRANTY

Up to 10 years unprecedented warranty.



OWN FACTORIES

Every step of the process is controlled by our European specialists at the factories.

DEVELOPMENT

Head office in Europe. Team of highly qualified specialists from defence, aviation, space and other specialized industries.



EXPERIENCE

Expert in the fields of mechanics, optics and electronics. We specialize in development and manufacturing of flashlights and battery chargers since 2009.



COMPONENTS

Components by world's leading manufacturers. Powerful LEDs, innovative electronics, aircraft-grade aluminium, tempered glass, etc.



SMART LINEUP

Simple process of choosing a product, no bulky catalogs with a lot of similar variants. Only best models for client's needs.



MEW PRODUCTS

Armytek produces innovative and the most technically advanced products in the world.



PRIVATE LABEL, OEM/ODM

Creating new products, modifying our production models and personalizing them according to your needs.




MARKETING SUPPORT

We provide all the necessary promotional materials: leaflets, booklets, catalogs, etc.



CLIENTS' NEEDS RESEARCH

We systematically gather feedback to make sure that our products completely fit clients' needs and requirements.



Armytek Wholesale Department



+1 (206) 260-12-66 +49 (30) 9173-48-39

+49 (16) 2426-34-98 🕓

Germany: Finland: Poland:

+49 (30) 9173-48-39

+48 (85) 876-07-10

+358 (94) 245-08-33 🕓 +48 (85) 876-08-79

world@armytek.com www.armytek.com



