

DOBERMANN PRO SAND



DOBERMANN PRO SAND



SPECIFICATIONS

		Dobermann Pro (Warm)
Optics		Smooth reflector
Light output		1400 lm
Beam distance		363 m
Hotspot : Spill		6°:40°
Brightness stabilization type		Full (constant light)
Number of modes		6
Modes / Runtimes	Turbo	1400 lm / 1 h 33 min (710 lm after 3 min)
	Main3	280 lm / 5 h 13 min
	Main2	112 lm / 12 h 20 min
	Main1	37 lm / 32 h
	Strobe2	1400 lm / 15 Hz / 3 h (710 lm after 3 min)
	Strobe1	112 lm / 15 Hz / 23 h
Power source		1x18650 Li-Ion
Length / head diameter / body diameter		150 mm / 33.5 mm / 25.4 mm
Weight without / with battery		114 g / 164 g
Ingress protection, Submersion and Impact resistance		IP68. Depth up to 25 m for 5 h. Height up to 25 m
Set description		Flashlight, 18650 Li-Ion battery 3500 mAh, magnetic USB charger, clip, lanyard, holster, silicone grip, 2 spare O-rings, user manual

► All the above specifications are test results based on ANSI/PLATO FL 1-2019 Standard using the battery in the set. The data may vary due to environment, heat dissipation and other factors.