

# WIZARD C2 PRO OLIVE



# WIZARD C2 PRO OLIVE



## SPECIFICATIONS

		Wizard C2 Pro (White)
<b>Optics</b>		TIR
<b>Light output</b>		2500 lm
<b>Beam distance</b>		131 m
<b>Hotspot : Spill</b>		70°:120°
<b>Brightness stabilization type</b>		Full
<b>Number of modes</b>		6 simple operation by default / 12 advanced operation
<b>Modes / Runtimes</b>	<b>Turbo3</b>	2500 lm / 2 h 40 min (650 lm after 30 sec)
	<b>Turbo2</b>	1750 lm / 2 h 45 min (650 lm after 2 min)
	<b>Turbo1</b>	870 lm / 2 h 50 min (650 lm after 9 min)
	<b>Main3</b>	370 lm / 5 h 15 min
	<b>Main2</b>	160 lm / 12 h 15 min
	<b>Main1</b>	45 lm / 43 h
	<b>Firefly3</b>	6 lm / 12 d
	<b>Firefly2</b>	1.5 lm / 40 d
	<b>Firefly1</b>	0.15 lm / 200 d
	<b>Strobe3</b>	2500 lm / 10 Hz / 5 h 45 min (650 lm after 100 sec)
	<b>Strobe2</b>	2500 lm / 1 Hz / 12 h (650 lm after 9 min)
	<b>Strobe1</b>	160 lm / 1 Hz / 55 h
<b>Power source</b>		1x18650 Li-Ion
<b>Length / head diameter / body diameter</b>		112 mm / 33 mm / 20.4 mm
<b>Weight without / with battery</b>		65 g / 115 g
<b>Ingress protection, Submersion and Impact resistance</b>		IP68. Depth up to 10 m for 5 h. Height up to 10 m

► The model is available with White and Warm light. Light output for flashlights with Warm light is about 7% less, beam distance is about 3% less.  
All the above specifications are test results based on ANSI/PLATO FL 1-2019 Standard. The data may vary due to environment, heat dissipation and other factors.