

WIZARD C2 PRO MAX OLIVE



WIZARD C2 PRO MAX OLIVE



SPECIFICATIONS

		Wizard C2 Pro Max (White)
Optics		TIR
Light output		4000 lm
Beam distance		114 m
Hotspot : Spill		110°:150°
Brightness stabilization type		Full
Number of modes		6 simple operation by default / 10 advanced operation
Modes / Runtimes	Turbo2	4000 lm / 3 h 15 min (900 lm after 50 sec)
	Turbo1	1300 lm / 3 h 20 min (900 lm after 12 min)
	Main3	450 lm / 7 h
	Main2	150 lm / 21 h
	Main1	45 lm / 64 h
	Firefly2	7 lm / 10 d
	Firefly1	0.6 lm / 62 d
	Strobe3	4000 lm/10 Hz/6 h 50 min (900 lm after 2 min)
	Strobe2	4000 lm/1 Hz/14 h (900 lm after 10 min)
	Strobe1	150 lm/1 Hz/90 h
Power source		1x21700 Li-Ion, 1x18650 Li-Ion
Length / head diameter / body diameter		121.5 mm / 34.4 mm / 23.6 mm
Weight without / with battery		79 g / 149 g
Ingress protection, Submersion and Impact resistance		IP68. Depth up to 10 m for 5 h. Height up to 10 m

- The model is available with White and Warm light. Light output for flashlights with Warm light is about 7% less, beam distance is about 3% less.
All the above specifications are test results based on ANSI/PLATO FL 1-2019 Standard. The data may vary due to environment, heat dissipation and other factors.