

# Pushbutton, 9.1 mm, 1NO+1NC, momentary contact function, 1 NC + 1 NO, bezel green



## fields of application

- > Mechanical and system engineering
- > Model construction
- > Home technology

## special features

Drucktaster opak, nicht beleuchtbar  
 Einbaudurchmesser 9,1, mm  
 max. 24 V / 100 mA  
 Lötanschluss  
 Befestigungstechnik mit Gewinding  
 Schutzart IP 40 frontseitig



## description

Pushbutton with mounting hole diameter 9.1 mm

Pushbutton with mounting hole diameter 9.1 mm, 1 NC + 1 NO

## technical data

### > general

Bezel color	green
Property of bezel / mushroom	opaque
Collar shape	round
Operating temperature, min.	-25 °C
Operating temperature, max.	70 °C
Storage temperature, min.	-40 °C
Storage temperature, max.	80 °C
illuminated	No
Soldering time for manual soldering, max.	3 sec
Soldering temperature for manual soldering	350 °C
Soldering	Manual soldering
Packaging	Box
Packaging unit	10 pcs.
net weight	2.2 g
Operating life	200,000 cycles
B10	260,000 cycles
Degree of protection, front side, according to DIN EN 60529	IP40
MOQ order	50 pcs.
RoHS compliant	Yes
REACH compliant	Yes

### direct links

- > RAFI eCatalog

### > mounting diameters

Outside dimension, length	11 mm
Outside dimension, width	11 mm
Outside dimension, height	32 mm
Mounting hole	9.1 mm
Mounting depth	25 mm
Installation height	7 mm

**> mechanical data**

Actuation function	momentary contact function
Operating force, max.	5 N
Operating force, min.	5 N
Operating travel, max.	1.5 mm
Contact function	1 NC + 1 NO
Contact system	Bridge contact
Contact material	Gold
Fixing	Threaded ring
Solderability	Yes
Terminal on the rear	Solder terminal

**> electrical data**

Rated voltage, max.	24 V
Rated current, max.	0.5 A