

## Pushbutton, 15.2 mm, quick connector, momentary contact function, 1 NO, bezel white



### fields of application

- > Mechanical and system engineering
- > Model construction
- > Home technology

### special features

Drucktaster opak, nicht beleuchtbar  
 Einbaudurchmesser 15,2, mm  
 max. 250 V / 700 mA  
 Schraub- oder Flachstecker-Anschluss  
 Befestigungstechnik mit Gewinding  
 Schutzart IP 40 frontseitig (IP 65 mit Schutzkappe)



### description

Pushbutton with mounting hole diameter 15.2 mm

Pushbutton with mounting hole diameter 15.2 mm, solder/quick-connect terminal for 6.3 x 0.8 mm or 2 x 2.8 x 0.8 mm

### technical data

#### > general

Bezel color	white
Property of bezel / mushroom	opaque
Collar shape	round
Operating temperature, min.	-25 °C
Operating temperature, max.	85 °C
Storage temperature, min.	-40 °C
Storage temperature, max.	90 °C
illuminated	No
Packaging	Box
Packaging unit	100 pcs.
net weight	5 g
Operating life	25,000 cycles
B10	32,500 cycles
Degree of protection, front side, according to DIN EN 60529	IP40 IP65 with sealing cap
MOQ order	100 pcs.
RoHS compliant	Yes
REACH compliant	Yes

#### direct links

> [RAFI eCatalog](#)

#### > mounting diameters

Outside dimension, length	19 mm
Outside dimension, width	19 mm
Outside dimension, height	29.7 mm
Mounting hole	15.2 mm

Mounting depth	21.5 mm
Installation height	8.2 mm
<b>&gt; mechanical data</b>	
Actuation function	momentary contact function
Operating force, max.	7.5 N
Operating travel, max.	3 mm
Contact function	1 NO
Contact system	Bridge contact
Contact material	Silver
Fixing	Threaded ring
Solderability	No
Terminal on the rear	Flat quick-connect terminal 6.3 x 0.8 / 2 x 2.8 x 0.8
<b>&gt; electrical data</b>	
Rated voltage, max.	250 V
Rated current, max.	0.7 A