

## Pushbutton, 16.2 mm, momentary contact function, 1 NO, bezel red



### fields of application

- > Mechanical and system engineering
- > Model construction
- > Home technology



### description

Pushbutton with mounting hole diameter 16.2 mm, screw terminal, non-illuminated

### technical data

#### > general

Bezel color	red
Property of bezel / mushroom	opaque
Collar shape	round
Operating temperature, min.	-25 °C
Operating temperature, max.	85 °C
Storage temperature, min.	-40 °C
Storage temperature, max.	90 °C
illuminated	No
Packaging	Box
Packaging unit	100 pcs.
net weight	11 g
Operating life	150,000 cycles
B10	195,000 cycles
Degree of protection, front side, according to DIN EN 60529	IP40 IP65 IP65 with sealing cap
MOQ order	100 pcs.
RoHS compliant	Yes
REACH compliant	Yes

#### direct links

- > RAFI eCatalog

#### > mounting diameters

Outside dimension, length	20 mm
Outside dimension, width	20 mm
Outside dimension, height	50 mm
Mounting hole	16.2 mm
Mounting depth	41 mm
Installation height	9 mm

#### > mechanical data

Actuation function	momentary contact function
Operating force, min.	7,5 N

Operating travel, max.	4.3 mm
Contact function	1 NO
Contact system	Bridge contact
Contact material	Silver
Fixing	Threaded ring
Terminal on the rear	Screw terminal

**> electrical data**

Rated voltage, max.	250 V
Rated current, max.	2 A

**drawings**

**Dimensioned drawing**

