

Signal lamp with lamp socket, BA 9s, 18.2 mm, round bezel, 250 Volt, bezel slate gray, Flat quick-connect terminal 6.3 x 0.8 / 2 x 2.8 x 0.8 tin-plated



fields of application

- › Measurement-control-regulation
- › Electrical engineering
- › Mechanical and system engineering
- › Signalling systems
- › Model construction



description

Signal lamps for LEDs or filament/neon lamps with BA 9 s socket, mounting hole diameter 18.2 mm

technical data

› general

Bezel color	slate gray
Property of bezel / mushroom	transparent
Bezel shape	round
illuminated	Yes
Lamp socket	BA9s
Packaging unit	10 pcs.
net weight	13.2 g
Degree of protection, front side, according to DIN EN 60529	IP65
MOQ order	250 pcs.
RoHS compliant	Yes
REACH compliant	Yes

direct links

- › [RAFI eCatalog](#)

› mounting diameters

Outside dimension, length	22 mm
Outside dimension, width	22 mm
Outside dimension, height	61 mm
Mounting hole	18.2 mm
Mounting depth	47 mm
Installation height	14 mm
Collar dimension	22 mm

› mechanical data

Fixing	Threaded ring
Solderability	Yes
Terminal on the rear	Flat quick-connect terminal 6.3 x 0.8 / 2 x 2.8 x 0.8 tin-plated

> **electrical data**

Operating voltage of the luminous element, max. 250 V

drawings

Mounting hole drawing