

Signal lamp with lamp socket, BA 15d, IP65, 30.5 mm, housing, 250 Volt, Screw/quick-connect terminal



fields of application

- > Measurement-control-regulation
- > Electrical engineering
- > Mechanical and system engineering
- > Signalling systems
- > Model construction

description

Signal lamps for LEDs and filament lamps with BA 15 d socket, mounting hole diameter 30.5 mm

technical data

> general

Bezel shape	round
illuminated	Yes
Lamp socket	BA 15d
Packaging unit	10 pcs.
net weight	28.1 g
Degree of protection, front side, according to DIN EN 60529	IP65
MOQ order	50 pcs.
RoHS compliant	Yes
REACH compliant	Yes

direct links

> [RAFI eCatalog](#)

> mounting diameters

Outside dimension, length	36 mm
Outside dimension, width	36 mm
Outside dimension, height	71 mm
Mounting hole	30.5 mm
Mounting depth	58 mm
Installation height	38 mm
Collar dimension	36 mm

> mechanical data

Fixing	Threaded ring
--------	---------------

Terminal on the rear

Screw/quick-connect terminal

> electrical dataOperating voltage of the luminous
element, max. 250 V

drawings

Mounting hole drawing