

# KERN FS 2-1KOY2



Pre-configured set consisting of the premium force gauge FS-2 and the measuring cell CO 100-Y2 (For tensile force and compressive force testing)



Mounting - force application	External thread M12
Mounting - force dissipation	External thread M12
Dimensions load cell (cylindrical)	51×70 mm

## Functions

Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
Peak function	✓
Statistic function	✓
Memory function	✓
Interfaces	USB-Device

## Power Supply

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	5 V, 1 A
Plug-in power supply type	USB including power supply
Supplied power supply	Battery & Power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
Rechargeable battery charging time	8 h
Rechargeable battery operating time - backlight on	5 h
Rechargeable battery operating time - backlight off	8 h
Battery / accumulator type	Li-Ion
Battery connection	2-pole tub connector
Battery capacity	2.400 mAh
Battery voltage	3,7 V

## Packing & Shipping

Readability force [d] (N)	3 d
Net weight	0,755 kg
Shipping method	Parcel service
Net weight approx.	0,80 kg
Gross weight approx.	1,8 kg
Shipping weight	1,643 kg

## Services (optional)

Article number for DAkkS calibration (tensile force)	963-162
Article number for DAkkS calibration (compressive force)	963-262
Article number for DAkkS calibration (tensile force/compressive force)	963-362

## Category

Brand	Sauter
Product category	Force measurement
Product group	Force measuring device set
Product family	FS OY2

## Measuring System

Default unit	N
Measuring range force [Max] (N)	1 kN
Readability force [d] (N)	0,2 N
Directions of force	tension compression
Measuring head measuring frequency	1000 Hz
Number of platforms / channels	2

## Approval

CE mark	✓
---------	---

## Display

Display type	TFT, color
Display resolution	320×480
Languages of the user interface	German English French Spanish Italian

## Construction

Material display housing	Plastics
Material housing	plastic


# KERN FS 2-1KOY2



Pre-configured set consisting of the premium force gauge FS-2 and the measuring cell CO 100-Y2 (For tensile force and compressive force testing)

## Pictograms

### STANDARD



### OPTION

