KERN FS 2-20KOY1



Pre-configured set consisting of the premium force gauge FS 2 and the measuring cell CO 2000-Y1 $\,$



Category	
Brand	Sauter
Product categoriy	Force measurement
Product group	Force measuring device set
Product family	FS OY1

Measuring System	
Default unit	N
Measuring range force [Max] (N)	20 kN
Readability force [d] (N)	4 N
Directions of force	compression
Measuring head measuring frequency	1000 Hz
Number of platforms / channels	2

Approval	
CE mark	✓

Display	
Display type	TFT, color
Display resolution	320×480
Languages of the user interface	German English French Spanish Italian

Construction	
Material display housing	Plastics
Material housing	plastic

Mounting - force application	Thrust piece (from customer side)
Mounting - force dissipation	3 × threaded hole M4
Dimensions load cell (cylindrical)	30×18 mm

Functions		
	Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
	Peak function	✓
	Statistic function	✓
	Memory function	✓
	Interfaces	USB-Device

Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	5 V, 1 A
Plug-in power supply type	USB including power supply
Supplied power supply	Battery & Power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
Rechargeable battery charging time	8 h
Rechargeable battery operating time - backlight on	5 h
Rechargeable battery operating time - backlight off	8 h
Battery / accumulator type	Li-lon
Battery connection	2-pole tub connector
Battery capacity	2.400 mAh
Battery voltage	3,7 V

Packing & Shipping	
Readability force [d] (N)	3 d
Net weight	0,397 kg
Shipping method	Parcel service
Net weight approx.	0,40 kg
Gross weight approx.	1,4 kg
Shipping weight	1,295 kg

Services (optional)	
Article number for factory calibration (compressive force)	961-264

1

KERN FS 2-20KOY1



Pre-configured set consisting of the premium force gauge FS 2 and the measuring cell CO 2000-Y1 $\,$

Pictograms

STANDARD



OPTION

