

# KERN IXC 10K-4



Convenience for industry: Stainless steel platform scales with up to four interfaces and intuitive operation



Load cell connection 4-wire

## Approval

CE mark ✓

## Display

Display type	LCD
Display type	LCD with backlight
Display screen size	160×60 mm
Display backlight	✓
Display digit height	48 mm
Languages of the user interface	English Symbol language

## Construction

Dimension display device (W×D×H)	232×150×80 mm
Dimensions weighing platform (W×D×H)	300×240×105 mm
Material display housing	stainless steel
Material weighing plate	stainless steel
Material platform	steel, varnished
Dimensions weighing surface (W×D)	300×240 mm
Display device cable length	3 m
Allowed cable length display device [Max]	3 m
Transport safety lock - bolt torque	0,1 Nm
Material load cell(s)	aluminium
Load cells - number	1
Levelling feet adjustable	✓
Wall mount	✓

## Functions

Number of keys for operation	7
Auto-off interval(s) in mains power mode	off
	5 min
	2 min
Auto-off interval(s) in battery mode/rechargeable battery mode	1 min
	30 min
	60 min
	30 sec
Capacity display	✓
PreTare function	✓
Tare function	manual (multi)
Hold function	✓
Percentage determination	✓
Counting function	✓

## Category

Brand	KERN
Product category	Industrial scale
Product group	Platform scale
Product family	IXC

## Measuring System

Construction type of the scale	Single-range balance
Number of weighing ranges	1
Weighing system	Strain gauge
Weighing capacity [Max]	15 kg
Readability [d]	0,0005 kg
Resolution	30.000
Linearity	± 0,0015 kg
Reproducibility	0,0005 kg
Default unit	kg

Units

- kg
- g
- lb
- ffa
- PCS
- %

Adjustment options	Adjusting with external weight
Recommended adjusting weight	15 kg (M1)
Possible calibration points	15 kg
Stabilization time	3 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,0015 kg
Maximum creep (15 minutes)	2 g
Maximum creep (30 minutes)	4 g
Loadcell type	aluminium silicone-coated

# KERN IXC 10K-4



Convenience for industry: Stainless steel platform scales with up to four interfaces and intuitive operation

Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Recipe/summing level	Sum A
Sum memory function	✓
Alibi memory	optional internal memory
Alibi memory - number of memory spaces	250.000
Interfaces	RS-232 (optional, factory) Bluetooth (optional, factory) Ethernet (optional, factory) WiFi (optional, factory) Alibi memory (optional, factory) analogue (0 - 10 V) (optional, factory) analogue (4 - 20 mA) (optional, factory) Bluetooth BLE (v4.0) (optional, factory) USB-Device (optional, factory)
IP protection - complete device	-
IP protection - display	IP68
IP protection - load cell	IP65
IP protection - platform	no IP protection

## Counting

Smallest piece weight when piece counting - laboratory conditions	500 mg
Smallest piece weight when piece counting - normal conditions	5 g
Counting reference weight can be entered	✓
Reference quantity	5, 10, 20, 50, n (any number of pieces)
Counting resolution (laboratory conditions)	30.000

## Power Supply

Input voltage power supply / power [Max]	110 V - 240 V AC
Plug-in power supply type	Built-in power supply
Supplied power supply	Power supply unit

Plug-in power supply / adapter for countries - included with the delivery	EURO
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	8 h
Rechargeable battery operating time - backlight on	20 h
Rechargeable battery operating time - backlight off	48 h
Battery	no battery
Battery / accumulator type	Li-Ion

## Environmental conditions

Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	490×570×212 mm
Net weight	5,1 kg
Shipping method	Parcel service
Net weight approx.	6 kg
Gross weight approx.	7 kg
Shipping weight	11,8 kg

## Services (optional)

Article number for adjustment at the location of installation	961-248
Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517


# KERN IXC 10K-4



Convenience for industry: Stainless steel platform scales with up to four interfaces and intuitive operation

## Pictograms

### STANDARD



### OPTION



### FACTORY

