

# KERN IXC 60K-2M



Convenience for industry: Stainless steel platform scales with up to four interfaces and intuitive operation, also with optional verification



## Approval

CE mark	✓
Pattern approval for conformity assessment	✓
Accuracy classe	III
Verification scale interval [e]	0,01 kg; 0,02 kg
Conformity assessment possible ex works	✓

## Display

Display type	LCD
Display type	LCD with backlight
Display screen size	160×60 mm
Display backlight	✓
Display digit height	48 mm
Languages of the user interface	English Symbol language

## Construction

Dimension display device (W×D×H)	232×150×80 mm
Dimensions weighing platform (W×D×H)	400×300×114 mm
Material display housing	stainless steel
Material weighing plate	stainless steel
Material platform	steel, varnished
Dimensions weighing surface (W×D)	400×300 mm
Display device cable length	3 m
Allowed cable length display device [Max]	3 m
Material load cell(s)	aluminium
Load cells - number	1
Levelling feet adjustable	✓
Wall mount	✓

## Functions

Number of keys for operation	7
Auto-off interval(s) in mains power mode	off
	5 min
	2 min
Auto-off interval(s) in battery mode/rechargeable battery mode	1 min
	30 min
	60 min
	30 sec
Capacity display	✓
PreTare function	✓
Tare function	manual (multi)

## Category

Brand	KERN
Product category	Industrial scale
Product group	Platform scale
Product family	IXC

## Measuring System

Conformity assessment possible	✓
Construction type of the scale	Multi-range balance
Number of weighing ranges	2
Weighing system	Strain gauge
Weighing capacity [Max]	30 kg; 60 kg
Readability [d]	0,01 kg; 0,02 kg
Resolution	3.000, 3.000
Linearity	± 0,01 kg; 0,02 kg
Reproducibility	0,01 kg; 0,02 kg
Default unit	kg
Units	kg
Units (if device is conformity assessed)	kg g
Minimum weight [Min]	0,2 kg; 0,4 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	60 kg (M1)
Possible calibration points	30 kg; 60 kg
Stabilization time	3 s
Warm-up time	10 min; 10 min
Eccentric loading at 1/3 [Max]	0,01 kg; 0,02 kg
Loadcell type	aluminium IP65 silicone-coated
Load cell connection	4-wire

# KERN IXC 60K-2M



Convenience for industry: Stainless steel platform scales with up to four interfaces and intuitive operation, also with optional verification

Hold function	✓
Percentage determination	✓
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Recipe/summing level	Sum A
Sum memory function	✓
Alibi memory	optional internal memory
Alibi memory - number of memory spaces	250.000
Interfaces	RS-232 (optional, factory)
	Bluetooth (optional, factory)
	Ethernet (optional, factory)
	WiFi (optional, factory)
	Alibi memory (optional, factory)
	analogue (0 - 10 V) (optional, factory)
	analogue (4 - 20 mA) (optional, factory)
	Bluetooth BLE (v4.0) (optional, factory)
	USB-Device (optional, factory)
	IP protection - complete device
IP protection - display	IP68
IP protection - load cell	IP65
IP protection - platform	no IP protection

<b>Counting</b>	
Smallest piece weight when piece counting - laboratory conditions	2 g
Smallest piece weight when piece counting - normal conditions	20 g
Counting reference weight can be entered	✓
Reference quantity	5, 10, 20, 50, n (any number of pieces)
Counting resolution (laboratory conditions)	30.000

<b>Power Supply</b>	
Input voltage power supply / power [Max]	110 V - 240 V AC
Plug-in power supply type	Built-in power supply

Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	8 h
Rechargeable battery operating time - backlight on	20 h
Rechargeable battery operating time - backlight off	48 h
Battery	no battery
Battery / accumulator type	Li-Ion

<b>Environmental conditions</b>	
Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

<b>Packing &amp; Shipping</b>	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	500×635×222 mm
Net weight	10,5 kg
Shipping method	Parcel service
Net weight approx.	11 kg
Gross weight approx.	14 kg
Shipping weight	14,1 kg

<b>Services (optional)</b>	
Article number for adjustment at the location of installation	961-249
Article number for conformity assessment	965-229
Article number for DAkkS calibration	963-129
Article number for certificate of conformity (verification)	969-517


# KERN IXC 60K-2M



Convenience for industry: Stainless steel platform scales with up to four interfaces and intuitive operation, also with optional verification

## Pictograms

### STANDARD



### OPTION



### FACTORY

