KERN **KFP 60V40LM**

Platform: entirely out of stainless steel



Category

Brand	KERN
Product categoriy	Component
Product group	Platform
Product family	KFP-V40-IP68

Measuring System

Weighing capacity [Max]	60 kg
Readability [d]	5 g
Minimum weight [Min]	200 g
Load cell connection	6-wire
Load cell - Resolution (verifiable)	2 × 3000 e
Load cell OIML class	C3
Loadcell type	stainless steel IP68 encapsulated

Construction

Dimensions weighing surface (W×D)	500×400 mm
Dimensions weighing surface	500×400 mm
Dimensions weighing platform (W×D×H)	500×400×126 mm
Material weighing plate	stainless steel
Material platform	stainless steel
Material load cell(s)	stainless steel
Levelling feet adjustable	✓
Cable length	3 m
Allowed cable length display device [Max]	20 m
Platform Construction	Single-Cell
Load cells - number	1

Functions

IP protection - platform	no IP protection
IP protection - load cell	IP68, IP69K

Approval

Conformity assessment possible ex works	✓
Verification scale interval [e]	10 g; 20 g

Services (optional)

Article number for conformity assessment	965-229
Article number for DAkkS calibration	963-129

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	930×550×230 mm
Shipping method	Parcel service
Net weight approx.	11 kg
Gross weight approx.	13 kg
Shipping weight	23,5 kg

Product information

GTIN/EAN number	4045761475960
REACH classification	no prohibited substances

Pictograms

STANDARD



FACTORY

