


KERN KFP 60V40M

Platform: entirely out of stainless steel

KERN



Category

Brand	KERN
Product category	Component
Product group	Platform

Measuring System

Weighing capacity [Max]	60 kg
Readability [d]	5 g
Minimum weight [Min]	200 g
Loadcell type	stainless steel IP68 encapsulated
Load cell connection	6-wire
Load cell OIML class	C3
Load cell - Resolution (verifiable)	2 × 3000 e

Approval

Verification scale interval [e]	10 g; 20 g
Conformity assessment possible ex works	✓

Construction

Dimensions weighing platform (W×D×H)	400×300×120 mm
Material weighing plate	stainless steel
Material platform	Stainless steel
Dimensions weighing surface (W×D)	400×300 mm
Cable length	3 m
Allowed cable length display device [Max]	20 m
Material load cell(s)	Stainless steels
Load cells - number	1
Levelling feet adjustable	✓

Functions

IP protection - load cell	IP68
IP protection - platform	no IP protection

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	800×465×230 mm
Net weight	7,2 kg
Shipping method	Parcel service
Net weight approx.	8 kg
Gross weight approx.	12 kg
Shipping weight	17,1 kg

Services (optional)

Article number for conformity assessment	965-229
Article number for DAkkS calibration	963-129

Pictograms

STANDARD



FACTORY

