

1 KERN KFS-TM

Professional indicator with 3 displays, verification optional

Features

- 99 item memories
- Totalising
- Printout with date and time
- Integrated KERN Communication Protocol (KCP), ideal for connecting an Merchandise Management or ERP system
- Compatible with KERN EasyTouch App
- Benchtop stand for display device incl.
- Wall mount for display device, standard

Discover more details and matching accessories online!

STANDARD

RS 232 · KCP · GLP · 1 DAY

OPTION

FACTORY



2 KERN KFN-TM

Stainless steel display device with IP65 protection and superior display size and optional analogue output for controlling systems (PLC) etc.

Features

- Totalising
- Hold function
- Benchtop stand for display device incl.
- Wall mount for display device, standard

*not possible in combination with verification. When installing the Bluetooth data interface, the RS-232 data interface can no longer be used

**not possible in combination with signal lamp. When installing the analogue module, the RS-232 data interface can no longer be used

STANDARD

KCP · IP 65 · 1 DAY

FACTORY

RS 232 · * · ** · M

KERN	1 KFS-TM	2 KFN-TM
Display (segments)	6 digits	5 + 1/2 digits
EU type approval	Yes	Yes
Resolution verifiable (e)	3.000	6.000
Terminal resolution (not verifiable)	60.000	30.000
Weighing capacities	2	2
Weighing units	kg, g	kg
Digit increments	1, 2, 5, 10, n	1, 2, 5, 10, n
Piece counting with reference	n	10, 20, 50, 100, 200
Display, digit height	LCD, 16,5 mm	LCD, 52 mm
Display backlight	yes	yes
Strain gauge load cells	87 – 1200 Ω	87 – 1600 Ω
Linearisation (points)	4	3
Input voltage	12 V, 500 mA	12 V, 500 mA
Permissible ambient temperature	0 °C – 40 °C	-10 °C – 40 °C
Dimensions housing W×D×H	250×160×65 mm	265,5×164,5×96 mm
Net weight	1,00 kg	2,6 kg