# KERN **OBB-A1592**

Eyepiece (Ø 30 mm): HWF 10x / Ø 20 mm (with scale 0,1 mm)




## Pictograms

**STANDARD**




## Category

| | |
|---|---|
| Brand | Optics |
| Product categoriy | Optical Instrument |
| Product group | Microscope eyepiece |

## Ocular

| | |
|---|---|
| Ocular field width | HWF |
| Eye point | High Eye Point |
| Ocular magnifications | 10x |
| Ocular visual field | 20 mm |
| Ocular scale | 0,1 mm |
| Ocular diameter | 30 mm |

## Environmental conditions

| | |
|---|---|
| Storage temperature [Min] | -5 °C |
| Storage temperature [Max] | 40 °C |

## Packing & Shipping

| | |
|---|---|
| Delivery time | 1 d |
| Dimensions packaging (W×D×H) | 85×65×45 mm |
| Shipping method | Parcel service |
| Net weight approx. | 0,10 kg |
| Gross weight approx. | 0,40 kg |
| Shipping weight | 0,4 kg |

## Product information

| | |
|---|---|
| GTIN/EAN number | 4045761249363 |
| REACH classification | no prohibited substances |