

KERN ORM 1HO

KERN

Digital measurement of refraction index for universal application



Category

Brand	Optics
Product category	Refractometer
Product group	Digital refractometer
Product family	ORM-HO

Measuring System

Automatic temperature compensation (ATC)	✓
Measuring method	Total reflection
Area of application	Honey
Appropriate calibration liquid	0 % (distilled water)
Measurement temperature [Min] (°C)	0 °C
Measurement temperature [Max] (°C)	40 °C
Brix scale	✓
Readout Brix	0,1 %
Measuring range Brix [Min]	0 %
Measuring range Brix [Max]	90 %
Accuracy Brix	±0,2 %
Scale for Refractive index	✓
Readout refractive index	0,0001 nD
Measuring range refractive index [Min]	1,3330 nD
Measuring range refractive index [Max]	1,5177 nD
Accuracy refractive index	±0,0003 nD
Scale for Baumé	✓
Readout Baumé	0,1 °Bé
Measuring range Baumé [Min]	33 °Bé
Measuring range Baumé [Max]	48 °Bé
Accuracy Baumé	±0,2 °Bé
Scale water content	✓
Readout water content	0,1 %

Measuring range water content [Min]	5 %
Measuring range water content [Max]	38 %
Accuracy water content	±0,2 %

Approval

CE mark	✓
---------	---

Construction

Dimension (W×D×H)	121×58×25 mm
Refractometer type	Handheld refractometer
Scale - Display type	Digital

Functions

Auto-off interval(s) in battery mode/rechargeable battery mode	60 sec
IP protection - complete device	IP65
Automatic temperature compensation	✓

Power Supply

Supplied power supply	Battery
Battery / accumulator type	Alkali(-Manganese)
Battery connection	Pad + Spring
Battery capacity	1.300 mAh
Battery voltage	1,5 V

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Dimensions transport container (W×D×H)	170×110×50 mm
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	170×110×50 mm
Net weight	0,14 kg
Shipping method	Parcel service
Net weight approx.	0,15 kg
Gross weight approx.	0,35 kg
Shipping weight	0,31 kg

Services (optional)

Article number for factory calibration	961-290
--	---------

KERN ORM 1HO



Digital measurement of refraction index for universal application

Pictograms

STANDARD

