## KERN OZL 473



The flexible, affordable all-rounder with flexible incident illumination for training workshops, inspection authorities and laboratories



Category	
Brand	Optics
Product categoriy	Microscope
Product group	Stereo microscope
Product family	OZL-47
Approval	
CE mark	$\checkmark$
Construction	
Dimension (W×D×H)	300×240×420 mm
Optical system	Greenough
Tube type	Binocular
Tube angle of inclination	45°
Tube 360° rotation	$\checkmark$
Eyepieces fixed	✓
Diopter adjustment	both-sided
Diopter adjustment [Min]	-5
Diopter adjustment [Max]	5
Contrasting methods	Bright field
Interpupillary distance [Max]	75 mm
Interpupillary distance [Min]	55 mm

## Ocular

ooalal	
Ocular field width	HWF
Eye point	High Eye Point
Ocular magnifications	10 x
Ocular visual field	20 mm
Ocular diameter	30 mm

Focussing	
Torque regulation	1
Working distance	105 mm
Zoom [Min]	0,7 x
Zoom [Max]	4,5 x
Magnification ratio	6,4:1
Field of view [Min]	4,4 mm
Field of view [Max]	28,6 mm
Focusing mechanism	coarse drive
Standard total magnification [Min]	7 x
Standard total magnification [Max]	45 x
Illumination	
Illumination type incident light	LED
Illumination intensity incident light	3 W
Illuminance	Reflected light
Illumination dimmable	Incident light
Power Supply	
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - optional	UK
Environmental conditions	
Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C
Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	452×414×290 mm
Net weight	4,085 kg
Shipping method	Parcel service
Net weight approx.	4,2 kg
Gross weight approx.	7 kg
Shipping weight	10,9 kg
Pictograms	
STANDARD	
OO D O O   360° BINO LED IL Z00M	230 V 1 DAY