

KERN SXC 100K-2M



Interlinked for industry of the future: Stainless steel platform scale with up to four data interfaces and optional alibi memory, with optional verification



Category

Brand	KERN
Product category	Industrial scale
Product group	Stainless steel platform scale
Product family	SXC

Measuring System

Weighing system	Strain gauge
Number of weighing ranges	2
Weighing capacity [Max]	60 kg; 150 kg
Readability [d]	0,02 kg; 0,05 kg
Reproducibility	0,02 kg; 0,05 kg
Linearity	± 0,02 kg; 0,05 kg
Minimum weight [Min]	0,4 kg; 1 kg
Conformity assessment possible	✓
Resolution	3.000, 3.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	150 kg (M1)
Stabilization time	3 s
Warm-up time	10 min; 10 min
Eccentric loading at 1/3 [Max]	0,02 kg; 0,05 kg
Load cell connection	6-wire
Units (if device is conformity assessed)	kg g ffa PCS %
Construction type of the scale	Multi-range balance
Units	kg g ffa PCS %
Default unit	kg
Loadcell type	stainless steel IP68 encapsulated

Display

Display type	LCD
Display type	LCD with backlight
Display backlight	✓
Display screen size	160×60 mm
Display segments	6
Display digit height	48 mm
Languages of the user interface	English Symbol language

Construction

Dimension display device (W×D×H)	232×150×77,3 mm
Dimensions weighing surface (W×D)	500×400 mm
Dimensions weighing surface	500×400 mm
Dimensions weighing platform (W×D×H)	500×400×126 mm
Material weighing plate	stainless steel
Material platform	stainless steel
Material display housing	stainless steel
Material load cell(s)	stainless steel
Level indicator	✓
Levelling feet adjustable	✓
Stand rotatable	no
Stand inclinable	no
Wall mount	✓
Display device cable length	3 m
Allowed cable length display device [Max]	20 m
Platform Construction	Single-Cell
Load cells - number	1

Functions

PreTare function	✓
Sum memory function	✓
Recipe/summing level	Sum A
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Alibi memory	optional internal memory
Alibi memory - number of memory spaces	250.000
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Counting resolution (laboratory conditions)	7.500

KERN SXC 100K-2M



Interlinked for industry of the future: Stainless steel platform scale with up to four data interfaces and optional alibi memory, with optional verification

Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	20 g
Smallest piece weight when piece counting - normal conditions	200 g
Reference quantity	5, 10, 20, 50, n (any number of pieces)
Hold function	✓
IP protection - complete device	-
IP protection - display	IP68
IP protection - platform	no IP protection
IP protection - load cell	IP68, IP69K
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min
	2 min
	1 min
	30 min
	60 min
Auto-off interval(s) in mains power mode	30 sec
	off
Tare function	manual (multi)
Number of keys for operation	7

Interface

Interfaces	RS-232 (optional, factory)
	Ethernet (optional, factory)
	WiFi (optional, factory)
	Alibi memory (optional, factory)
	analogue (0 - 10 V) (optional, factory)
	analogue (4 - 20 mA) (optional, factory)
	Bluetooth BLE (v4.0) (optional, factory)
	USB-Device (optional, factory)
	compatible with EasyTouch
	✓

Power Supply

Supplied power supply	Power supply unit
Power supply type	Built-in power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
Input voltage power supply / power [Max]	110 V - 240 V AC
Power supply cable removable	fixed connection

Power socket for mains adapter	Cable permanently installed
Battery / accumulator type	Li-Ion
Battery	no battery
Rechargeable battery operating time - backlight on	20 h
Rechargeable battery operating time - backlight off	48 h
Rechargeable battery charging time	8 h
Rechargeable battery optional	Rchrg. battery optional - intern

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %

Approval

CE mark	✓
Conformity assessment possible ex works	✓
Accuracy classe	III
Verification scale interval [e]	0,02 kg; 0,05 kg

Services (optional)

Article number for adjustment at the location of installation	961-249
Article number for conformity assessment	965-229
Article number for DAkkS calibration	963-129
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	930×555×225 mm
Shipping method	Parcel service
Net weight approx.	12 kg
Gross weight approx.	15 kg
Shipping weight	23,2 kg

Product information

GTIN/EAN number	4045761359086
REACH classification	no prohibited substances


KERN SXC 100K-2M



Interlinked for industry of the future: Stainless steel platform scale with up to four data interfaces and optional alibi memory, with optional verification

Pictograms

STANDARD



OPTION



FACTORY

