SAUTER **TN GOLD 80**

Ultrasonic measuring instrument for checking the authenticity of gold bars and coins



Category

Brand	Sauter
Product categoriy	Material thickness measuring device
Product group	Ultrasonic Material thickness gauge pulse-echo method
Product family	TN-GOLD

Measuring System

Material thickness pulse-echo [Max] (mm)	80 mm
Readability material thickness [d] (mm)	0,01 mm
Speed of sound [Min] (m/s)	1000 m/s
Speed of sound [Max] (m/s)	9999 m/s
Measuring head diameter	6 mm
Measuring head measuring frequency	7 MHz
Internal data memory: Number of value groups	20
Units	mm inch
Tolerance (% of [Max])	0,5%
Internal data memory: Number of individual values	100
Material thickness pulse-echo [Min] (mm)	0,75 mm

Display

Display type	LCD
Display type	LCD
Display digit height	14 mm

Construction

Dimension (W×D×H)	150×74×32 mm
Dimension housing (W×D×H)	150×74×32 mm
Dimensions completely mounted (W×D×H)	150×74×32 mm
Dimension display device (W×D×H)	150×74×32 mm
Material housing	plastic
Material display housing	plastic
Cable length	0,9 m

Functions

Auto-off interval(s) in battery mode/rechargeable battery mode	1 - 60 min

Interface

Interfaces	USB-Device

Power Supply

Supplied power supply	Battery
Battery / accumulator type	Alkali(-Manganese)
Battery	2×1.5 V AA
Battery connection	Pad + Spring
Battery operating time	100 h
Battery capacity	3.000 mAh
Battery voltage	1,5 V
Battery – Number of cells	2
Battery – Individual weight	46 g
Battery – Total weight	92 g
Battery – Construction	Individual cells
Battery capacity (Wh)	4,5 Wh
Battery/Accu connected	not connected, enclosed

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓

Services (optional)

Article number for factory calibration	961-113

SAUTER **TN GOLD 80**

Ultrasonic measuring instrument for checking the authenticity of gold bars and coins

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	375×220×95 mm
Shipping method	Parcel service
Net weight approx.	0,25 kg
Gross weight approx.	1,4 kg
Shipping weight	1,6 kg

Product information

GTIN/EAN number	4045761210660
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

