# KERN **YKA-29**

External mains adapter CH, EU



| Category | |
|---|---|
| Brand | KERN |
| Product categoriy | Balance |
| Product group | Power adapter |

| Approval | |
|---|---|
| CE mark | ✓ |

| Construction | |
|---|---|
| Dimension (W×D×H) | 47×75×33 mm |
| Material | plastic |
| Cable length | 1,5 m |

| Power Supply | |
|---|---|
| Input voltage power supply / power [Max] | 100 - 240 V AC 50/60 Hz 0.8 A |
| Input voltage device / power [Max] | 12 V, 500 mA |
| Plug-in power supply type | Power adapter |
| Plug-in power supply / adapter for countries - included with the delivery | EURO<br>CH |

| Environmental conditions | |
|---|---|
| Storage temperature [Min] | -20 °C |
| Storage temperature [Max] | 60 °C |

| Packing & Shipping | |
|---|---|
| Readability force [d] (N) | 1 d |
| Dimensions packaging (W×D×H) | 134×65×56 mm |
| Net weight | 0,0628 kg |
| Shipping method | Parcel service |
| Net weight approx. | 0,10 kg |
| Gross weight approx. | 0,10 kg |
| Shipping weight | 0,1 kg |

## Pictograms