



Category

Brand	KERN
Product category	Balance
Product group	Power adapter

Approval

CE mark	✓
---------	---

Construction

Dimension (W×D×H)	70×70×40 mm
Material	plastic
Cable length	2 m

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 1.6 A
Plug-in power supply type	Power adapter
	EURO
Plug-in power supply / adapter for countries - included with the delivery	AUS UK US CH

Environmental conditions

Storage temperature [Min]	-10 °C
Storage temperature [Max]	50 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	120×150×63 mm
Net weight	0,23 kg
Shipping method	Parcel service
Net weight approx.	0,25 kg
Gross weight approx.	0,25 kg
Shipping weight	0,25 kg

Pictograms

STANDARD

