

# KERN YKG-01

Dot matrix printer

# KERN



## Category

|                  |         |
|------------------|---------|
| Brand            | KERN    |
| Product category | Balance |
| Product group    | Printer |

## Construction

|                   |                |
|-------------------|----------------|
| Dimension (W×D×H) | 160×245×140 mm |
| Material          | plastic        |

## Interface

|            |                 |
|------------|-----------------|
| Interfaces | RS-232 standard |
|------------|-----------------|

## Power Supply

|                                                                           |                              |
|---------------------------------------------------------------------------|------------------------------|
| Supplied power supply                                                     | Power supply unit            |
| Power supply type                                                         | Power adapter                |
| Plug-in power supply / adapter for countries - included with the delivery | EURO                         |
| Plug-in power supply / adapter for countries - optional                   | UK                           |
| Input voltage power supply / power [Max]                                  | 100 V - 240 V AC, 50 / 60 Hz |
| Power supply cable removable                                              | removable                    |
| Input voltage device / power [Max]                                        | 24 V DC 1,5 A                |
| Power socket for mains adapter                                            | 3-pole round plug            |

## Environmental conditions

|                           |       |
|---------------------------|-------|
| Ambient temperature [Min] | 5 °C  |
| Ambient temperature [Max] | 35 °C |

## Approval

|         |   |
|---------|---|
| CE mark | ✓ |
|---------|---|

## Packing & Shipping

|                              |                |
|------------------------------|----------------|
| Delivery time                | 1 d            |
| Dimensions packaging (W×D×H) | 330×300×220 mm |
| Shipping method              | Parcel service |
| Net weight approx.           | 2,8 kg         |
| Gross weight approx.         | 3,8 kg         |
| Shipping weight              | 4,4 kg         |

## Product information

|                      |                          |
|----------------------|--------------------------|
| GTIN/EAN number      | 4045761253056            |
| REACH classification | no prohibited substances |

## Pictograms

### STANDARD

