

4G Mobile WiFi E5785 Specification



■ Highlights

- Zero Touch, Plug & Play
- LTE Cat7, 300Mbps DL | 100Mbps UL
- WiFi 802.11ac/n , up to 32users access simultaneously
- 3000mAh battery, longer standby and working time
- HUAWEI AI Life APP , easy manager the device

Form Factor	Size: 108*62*17.1mm
Speed	LTE Cat7 DL/UL 2CC FDD-LTE: 300Mbps(DL), 100Mbps(UL) TDD-LTE: 220Mbps(DL), 20Mbps(UL) DL 64QAM, UL 16QAM
Band	E5785-320a LTE: B1/3/5/7/8/18/19/20/28/32/38/40/41/42 UMTS: B1/5/8 No GSM UL:3C/7C/38C/40C/41C DL:1C/3C/7C/38C/40C/41C/42C/3A-3A/41A-41A/1A-3A/1A-5A/1A-7A/1A-8A/1A-20A/1A-28A/3A-5A/3A-7A/3A-8A(B8 only SCC)/3A-20A/3A-28A/7A-8A(B8 only SCC)/7A-20A/7A-28A/8A-38A(B38 only SCC)/20A-32A(B32 only SCC)/20A-38A
Basic Feature	Battery Capacity : 3000mAh, Working time:12h
	Display : 1.45inch LCD
	1*Micro USB, 1*SIM card slot (3FF)
	1*Power KEY/1*Reset KEY/1*Menu KEY
	Accessories : 17cm USB charging line , 5V/2A charger (optional)
WiFi	802.11 b/g/n 2*2 MIMO 2.4GHz & 802.11a/n/ac 2*2 MIMO 5GHz , Support 32 user