

DATASHEET

ESD Board Holder



Item no. 3069293	Item no. 3069294	
		
Item no. 3594628	Item no. 3594629	Item no. 3594630
		

Technical data

Item No.	Dimensions (mm)	Each Slot Size(mm)	Depth (mm)	Width (mm)	Pitch (mm)	No. of PCB	Weight (kg)
3069293	355 x 268 x 128	155 x 75	5	2.5	9.5	25	0.65
3069294	265 x 205 x 95	155 x 75	5	3.2	9	25	0.46
3594628	485 x 175 x 50	175 x 3	7	3	16	25	0.5
3594629	410 x 280 x 165	225 x 2.8	5	2.8	10	38	1.7
3594630	410 x 140 x 22	140 x 2.8	5	2.8	10	42	0.31

Surface resistance.....10(4) - 10(9) Ω
 Standard.....DIN EN 61340-5-1
 Operating conditions.....0 to +40 °C, 0 - 85% (relative, non-condensing)
 Storage conditions.....-20 to +40 °C, 0 - 85% (relative, non-condensing)