

# Datasheet

Manufacturer Part No.: T24CA010 ... 018

## Polyester Braided Sleeving (Reel)



This cable bundling sleeve is the optimal and cost-effective solution when it comes to protecting and bringing together cables and wires. This flexible cable sleeving can also be used as an abrasive protection and as an inhibitor of animal bites.

The tightly woven braid hugs the contents and keeps them together, protected and clean. The material is weather resistant, durable and looks good doing it! The application is very simple and can be customized by shortening to the desired length. The cut can be made using the hot cutting method or by means of scissors / string cutter and subsequent heat sealing of the open ends. It is possible to lead out individual cables on the track through the slot. The rolls are ideal for industrial requirements or large projects.

**To prevent fraying, the sleeve should be cut with a hot cutting tool!**

**Technical data:** Material: polyester braid • Temperature range: -55 ... 155 °C • Melting temperature: 230 °C • Color: black • Tensile strength max. 10.4 MPa • RoHS compliant, REACH compliant, halogen free • Flammability class based on UL94HB.

Item-No.	GTIN	Bundle Ø min.	Bundle Ø max.	Complete reel Content
T24CA010	4260732285755	3 mm	4 mm	100 m
T24CA011	4260732285762	6 mm	7 mm	100 m
T24CA012	4260732285779	9 mm	10 mm	100 m
T24CA013	4260732285786	13 mm	14 mm	100 m
T24CA014	4260732285793	19 mm	20 mm	50 m
T24CA015	4260732285809	25 mm	26 mm	50 m
T24CA016	4260732285816	32 mm	33 mm	50 m
T24CA017	4260732285823	38 mm	39 mm	25 m
T24CA018	4260732285830	50 mm	51 mm	25 m