

# Datasheet

Manufacturer Part No.: T24CA023 ... T24CA033

## Polyester Braided Sleeving (Reel) Part-No.: T24CA023 – T24CA033



This cable braided sleeve is the optimal and cost-effective solution when it comes to protecting and bringing together cables and wires. This flexible cable sleeving can also be used as an abrasive protection and as an inhibitor of animal bites. The tightly woven braid hugs the contents and keeps them together, protected and clean. The material is weather resistant, durable and looks good doing it! The application is very simple and can be customized by shortening to the desired length. The cut can be made using the hot cutting method or by means of scissors / string cutter and subsequent heat sealing of the open ends. It is possible to lead out individual cables on the track through the slot.

**To prevent fraying, the sleeve should be cut with a hot cutting tool!**

**Technical data:** Material: polyester braid • Temperature range: -55 ... 155 °C • Melting temperature: 230 °C • Color: black • Tensile strength max. 10.4 MPa • RoHS compliant, REACH compliant, halogen free • Flammability class based on UL94HB.

Part-No.	Description	Bundle Ø	Bundle Ø max.	Reel Content	EAN/GTIN
T24CA023	Braided Sleeving 5 mm Black, PES (100m)	5 mm	6 mm	100 m	4260732285885
T24CA024	Braided Sleeving 8 mm Black, PES (100m)	8 mm	9 mm	100 m	4260732285892
T24CA025	Braided Sleeving 10 mm Black, PES (100m)	10 mm	11 mm	100 m	4260732285908
T24CA026	Braided Sleeving 13 mm Black, PES (100m)	13 mm	14 mm	100 m	4260732285915
T24CA027	Braided Sleeving 16 mm Black, PES (100m)	16 mm	17 mm	100 m	4260732285922
T24CA028	Braided Sleeving 19 mm Black, PES (50m)	19 mm	20 mm	50 m	4260732285939
T24CA029	Braided Sleeving 25 mm Black, PES (50m)	25 mm	26 mm	50 m	4260732285946
T24CA030	Braided Sleeving 29 mm Black, PES (50m)	29 mm	30 mm	50 m	4260732285953
T24CA031	Braided Sleeving 32 mm Black, PES (50m)	32 mm	33 mm	50 m	4260732285960
T24CA032	Braided Sleeving 38 mm Black, PES (25m)	38 mm	39 mm	25 m	4260732285977
T24CA033	Braided Sleeving 50 mm Black, PES (25m)	50 mm	51 mm	25 m	4260732285984