

# Datasheet

Manufacturer Part No.: T24CA034 ... T24CA047

## Expandable PET Braided Sleeving (Reel)

### No.: T24CA034 – T24CA047



This cable braided sleeve is the optimal and cost-effective solution when it comes to protecting and bringing together cables and wires. This high flexible cable sleeving can also be used as an abrasive protection and as an inhibitor of animal bites.

The woven braid hugs the contents and keeps them together, protected and clean. The material is weather resistant, durable and looks good doing it! The application is very simple and can be customized by shortening to the desired length. The cut can be made using the hot cutting method or by means of scissors / string cutter and subsequent heat sealing of the open ends.

**To prevent fraying, the sleeve should be cut with a hot cutting tool!**

**Technical data:** Material: polyester braid, high flexible (PET) • Temperature range: -55 ... 155 °C • Melting temperature: 230 °C • Color: black • RoHS compliant, REACH compliant, halogen free • Flammability class based on UL94HB.

Part-No.	Description	Expansion range	Flat width	Reel content	EAN/GTIN
T24CA034	Expandable Braided Sleeve 1...6 mm, Black (500 m)	1 ... 6 mm	4 mm	500 m	4260732285991
T24CA035	Expandable Braided Sleeve 4...8.5 mm, Black (500 m)	4 ... 8,5 mm	6 mm	500 m	4260732286004
T24CA036	Expandable Braided Sleeve 5...16 mm, Black (350 m)	5 ... 16 mm	8 mm	350 m	4260732286011
T24CA037	Expandable Braided Sleeve 7...19 mm, Black (350 m)	7 ... 19 mm	10 mm	350 m	4260732286028
T24CA038	Expandable Braided Sleeve 8...24 mm, Black (250 m)	8 ... 24 mm	12 mm	250 m	4260732286035
T24CA039	Expandable Braided Sleeve 10...27 mm, Black (200 m)	10 ... 27 mm	16 mm	200 m	4260732286042
T24CA040	Expandable Braided Sleeve 14...30 mm, Black (200 m)	14 ... 30 mm	20 mm	200 m	4260732286059
T24CA041	Expandable Braided Sleeve 18...35 mm, Black (200 m)	18 ... 35 mm	25 mm	200 m	4260732286066
T24CA042	Expandable Braided Sleeve 20...55 mm, Black (150 m)	20 ... 55 mm	32 mm	150 m	4260732286073
T24CA043	Expandable Braided Sleeve 30...60 mm, Black (100 m)	30 ... 60 mm	38 mm	100 m	4260732286080
T24CA044	Expandable Braided Sleeve 35...75.5 mm, Black (100 m)	35 ... 75,5 mm	45 mm	100 m	4260732286097
T24CA045	Expandable Braided Sleeve 40...80 mm, Black (100 m)	40 ... 80 mm	50 mm	100 m	4260732286103
T24CA046	Expandable Braided Sleeve 45...105 mm, Black (100 m)	45 ... 105 mm	64 mm	100 m	4260732286110
T24CA047	Expandable Braided Sleeve 63.5...120.7 mm, Black (100 m)	63.5 ... 120,7 mm	76 mm	100 m	4260732286127