

Big Digit Hygro-Thermometer

Large 1" Digits on Dual LCD
 Display Humidity and Temperature

Features:

- 1" digits displayed on Large LCD (3.1 x 2.4"/80 x 62mm) provide simultaneous measurements of humidity and temperature
- Memory with reset function stores maximum and minimum measurements
- Measuring range:
 Temperature 14 to 140°F (-10 to 60°C)
 Humidity 10% to 99% RH
- Accurate to 5% RH, 1°C, and 1.8°F (@ 0 to 50°C/32 to 122°F)
- °C/°F switchable temperature measurements
- Low battery indication
- Dimensions: 4.3 x 3.9 x 0.78" (110 x 100 x 20mm)
- Weight 6oz (169g)
- Complete with built-in tilt stand, wall mounting bracket, and 1.5V AAA battery

Applications:

- Use in factories, greenhouses and offices to maintain proper temperature and humidity conditions and to record extremes during the day.



Specifications:	Range
Humidity range	10 to 99%RH
Basic RH accuracy	± 5% (25 to 80%)
Temperature range	14 to 140°F (-10 to 60°C)
Basic Temperature Accuracy	+/-1.8F/1°C (14 to 122°F)
Dimensions	4.3 x 3.9 x 0.78"(109 x 99 x 20mm)
Weight	6oz (169g)

Ordering Information:

445703Big Digit Hygro Thermometer

