



# Cell PT

IPC-K9EP-3T0WE IPC-K9EN-3T0WE

### 3MP H.265 Wi-Fi Battery Camera

The Cell PT set up with 2.4GHz Wi-Fi is a 100% wire-free rechargeable camera that delivers well-rounded home protection for up to almost 365 days on one single charge. With 2K, IP66 Weatherproof, the Cell PT outdoor provides a huge field of view so you can see every corner of your home. Equipped with a built-in microphone and speaker, the outdoor camera allows you to listen and talk to anyone. Easy wireless installation—no need to connect your security camera to electrical wiring. Compatible with Amazon Alexa.



### 3MP QHD Video

See more details than 1080P



### Siren & Spotlight

Once an intruder is detected, the camera's spotlights and siren will be triggered or manually activated to warn off the would-be criminal.



#### Two-way Talk

Using variable sound when taking real-time talk with people in front of the camera



#### IP44

Weatherproof for outdoor conditions



### 100% Wire-Free

Supports 2.4 GHz Wi-Fi, Free of network cabling and power wiring hassles



#### PIR+Human Detection

Discerns people and motion detection. More accurate alerts.



#### Auto Tracking

(up to 256GB).

Track moving targets in time.

Flexible and Secure Storage

insert a micro SD card for local storage



### Type-C

**Battery Power** 

Type-C interface with better adaptability.

Informs you when battery level goes down

to 20%, 10%, so you can charge it in time.

15000mAh Rechargeable Battery

DC 5V Power Supply Rechargeable

**Low-Battery Notifications** 



### Works with Solar Panel


Works with Imou Solar Panel for battery charging



### Stay close with what you care

With Cloud service, you will have access to what you care as long as Internet is available. You can record daily or motion videos on Cloud and play back anytime anywhere.





## Specifications

### Camera

3MP(2304\*1296)

Night Vision: 20m(23ft) Distance

3.6mm Fixed Lens

Field of View : 88° (H), 45° (V), 107° (D), (330° Pan, 90° Tilt )

### Video & Audio

Video Compression: H.265 Up to 15fps Frame Rate

8x Digital Zoom

Two-way Audio

### Notice Management

Motion Detection

**Human Detection** 

Configurable Region

Performance mode

Local Storage: SD Card (Up to 256GB)

Record, view, and save events in your Imou app with a 31 day trial of the Imou Subscription Plan.

### Storage

Cloud Storage: Imou Subscription Plan

### What's in the box

- 1x Camera
- 1x Power Cable (1m)
- 1x Mounting Template
- 4x Screws

- 1x Quick Start Guide
- 1x Mouting Bracket
- 4x Expansion Screw

### Network

Wi-Fi:IEEE802.11b/g/n,50m Open Field

Imou App: iOS, Android

### **Auxiliary Interface**

Built-in Mic & Speaker

Power on / off Button

Reset Button

### General

DC 5V 2A Power / Imou Solar Panel Supply

Power Consumption: < 3.5W

Operating Temperature: -20°C~+50°C (-4°F~122°F) Charging Temperature:  $-0^{\circ}C^{+45^{\circ}C}$  (32°F $^{-112^{\circ}F}$ )

Camera Dimensions:  $XX \times XX \times XX$ mm ( $XX \times XX \times XX$  inch)

Camera Weight: XXg (XXXIb)

FCC,CE,IC...

