



TOOLCRAFT

DATASHEET

Solder Fume Extractor

Item No. 3089719

Delivery

- Smoke extractor
- Exhaust air guide
- Extraction hose
- Extraction hood
- 1x Dust filter (installed)
- 1x PM2.5 filter (installed)
- 1x Odour filter (installed)
- 3x Spare dust filters
- Power adaptor
- Operating instructions



Technical data

Product

Input voltage	12 V/DC
Power consumption	15 W
Noise emission	max. 60 dB
Air flow rate	max. 17.2 m ³ /h
Vacuum	max. 0.7 kPa
Operating temperature	0 to +40 °C
Operating humidity	10 - 90 % RH (non-condensing)
Storage temperature	0 to +40 °C
Storage humidity	10 - 90 % RH (non-condensing)
Extraction hose length	66 cm
Dimensions (W x H x D)	210 x 90 x 210 mm
Weight (approx.)	1.28 kg

Power supply

Input voltage	100 - 240 V/AC, 50/60 Hz
Output voltage	12 V/DC
Output power	24 W

Filters

Dust filter	PM50, 50 µm
	175 x 175 x 5 mm
Fine particle filter	PM2.5, 2.5 µm
	175 x 175 x 15 mm
Odour filter	activated carbon
	175 x 175 x 10 mm

