

Item no.: 3089723

Data Sheet

USB to RS485, 422, FTDI-Chip



- Data Rate: 3M Baud
- Interface: RS485 / RS422
- End connector: Terminal block
- Cable details: UL2725 28#* 1P+24#*2C + A L + D + B (16*3/0.12AM) OD=4.5 mm
- Channel: 1
- USB Class: FTDI Drivers
- Max power output: RS485/422 +12 V -7 V
- ESD: 4 kV
- Operating temperature: -10 – 55 °C
- USB speed: Full speed
- USB Connector: USB AM
- Cable length: 1 m
- I/O voltage: 5 V
- Virtual Com port: yes
- FTDI internal IC: RT232RL

Data Sheet

