

VOLTCRAFT - TOP PERFORMANCE IN EVERY WAY

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

VT-300 **Telescopic Non-Contact** **Voltage Tester**

CE

Item no: 3124330

The product is a non-contact voltage tester with a telescopic testing head. Never use this product instead of a dedicated voltage meter to check if live voltage is present.

The product is intended to be used within the specifications of measuring category CAT II.



TECHNICAL DATA

	Unit	Value
Batteries		2x 1.5 V LR41 Button cell battery
Protection class		II
Voltage range for NCV	V/AC	70 - 250
Frequency range for NCV	Hz	50 - 500
Voltage range for polarity check	V/DC	3.0 - 30
Continuity check		Yes
Extension length (max.)	cm	130
Operation temperature	°C	-10 to +50
Operating humidity	% RH	<80
Storage temperature	°C	-10 to +50
Storage humidity	% RH	<80
Dimensions (L x W x H) (contracted)	mm	180 x 32 x 17
Weight	g	76

FEATURES

Non-contact voltage testing // Polarity checks of low voltage DC power sources // Continuity testing

CONTENTS

Product (with batteries installed) // Operating instructions

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method (e.g. photocopying, microfilming or the capture in electronic data processing systems) requires prior written approval from the editor. Reprinting, also in part, is prohibited. This publication reflects the technical status at the time of printing.

Copyright by Conrad Electronic SE.

*3124330_V1_0525_en_ds 2145602955 I1/O1 en