



POWER ADAPTER W24AA

Wall charger

(Intenso)[®]
for everyday life

QUALITY AUDIT
Tested in Germany ✓

Technical details

| | |
|--------------------------------------|--|
| Colour: | white |
| Surface: | plastic |
| Input connector: | EU Connector |
| Input voltage: | 100 - 240 V |
| Input alternating current frequency: | 50 / 60 Hz |
| Connections: | USB-A 1, USB-A 2 |
| Output: | USB-A 1: 5.0 V/DC 2.4 A, max. 12.0 W USB-A 2: 5.0 V/DC 2.4 A, max. 12.0 W USB-A 1+2: 2x 5.0 V/DC 2.4 A, max. 24.0 W |
| Average efficiency: | 86.50% |
| Efficiency at low load (10%): | 82.99% |
| Power consumption at no load: | <0,3 W |
| Dimensions: | 78 x 42 x 27 mm |
| Weight: | 62.0 g |
| Packing unit: | 2pcs |

Product data

| Colour | Article no | EAN |
|--------|------------|-----------------|
| white | 7802412 | 4 034303 033256 |