



## POWER ADAPTER W30AC

Fast Charger

(Intenso)<sup>®</sup>  
for everyday life

**QUALITY AUDIT**  
Tested in Germany ✓

### Technical details

Colour:	white
Surface:	plastic
Input connector:	EU connector
Input voltage:	100 - 240 V
Input alternating current frequency:	50 / 60 Hz
Connections:	USB-A, USB-C
Output:	supports (downwards compatible) PD 3.0, PPS und QC 4.0
	USB-A: 5.0 V/DC 3.0 A, max. 15.0 W 9.0 V/DC 2.0 A, max. 18.0 W 12.0 V/DC 1.5 A, max. 18.0 W
	USB-C: 5.0 V/DC 3.0 A, max. 15.0 W 9.0 V/DC 3.0 A, max. 27.0 W 12.0 V/DC 2.5 A, max. 30.0 W 15.0 V/DC 2.0 A, max. 30.0 W 20.0 V/DC 1.5 A, max. 30.0 W
	PPS: 3.3 – 11.0 V/DC 2.75 A, max. 30.0 W 3.3 – 16.0 V/DC 1.75 A, max. 30.0 W
	USB-A + USB-C: 5.0 V/DC 3.0 A, max. 15.0 W Total: max. 15.0 W (shared)
Average efficiency:	87.19%
Efficiency at low load (10%):	75.86%

Power consumption at no load:	<0.15 W
Dimensions:	80 x 41 x 26 mm
Weight:	58.0 g
Packing unit:	2 pcs

### Product data

Colour	Article no	EAN
white	7803012	4 034303 033287