



POWER ADAPTER W30C GaN

Fast Charger

(Intenso)[®]
for everyday life

QUALITY AUDIT
Tested in Germany ✓

Technical details

Colour:	white
Surface:	plastic
Input connector:	EU connector
Input voltage:	100 - 240 V
Input alternating current frequency:	50 / 60 Hz
Connections:	USB-C
Output:	supports (downwards compatible) PD 3.0, PPS and QC 4.0 5.0 V/DC 3.0 A, max. 15.0 W 9.0 V/DC 3.0 A, max. 27.0 W 12.0 V/DC 2.5 A, max. 30.0 W 15.0 V/DC 2.0 A, max. 30.0 W 20.0 V/DC 1.5 A, max. 30.0 W PPS: 3.3 – 11.0 V/DC 3.0 A, max. 30.0 W 3.3 – 16.0 V/DC 2.0 A, max. 30.0 W
Average efficiency:	90.09%
Efficiency at low load (10%):	81.22%
Power consumption at no load:	<0.1 W
Dimensions:	35.92 x 68.2 x 32.2 mm
Weight:	48.5 g
Packing unit:	2 pcs

Product data

Colour	Article no	EAN
white	7803022	4 034303 033317

What is GaN?



GaN adapters are a new type of power adapter that have many advantages compared to conventional, silicon-based adapters. GaN stands for Gallium Nitride, a material with a higher power density and efficiency. The use of GaN enables smaller power adapters that can also handle higher voltages and currents and even produce less heat.

This makes our power adapters with **GaN** technology **smaller, faster** and above all, more **energy efficient!**