

# (Intenso)<sup>®</sup>

for everyday life



## 30 W POWER ADAPTER DOUBLE PACK

2x W30C GaN

(Intenso)<sup>®</sup>  
for everyday life

**QUALITY AUDIT**  
Tested in Germany ✓

### Technical details

Colour:	white
Surface:	plastic
Input connector:	EU connector
Input voltage:	100 - 240 V
Input alternating current frequency:	50 / 60 Hz
Connections:	USB-C
Output:	supports (downwards compatible) PD 3.0, PPS and QC 4.0 5.0 V/DC 3.0 A, max. 15.0 W 9.0 V/DC 3.0 A, max. 27.0 W 12.0 V/DC 2.5 A, max. 30.0 W 15.0 V/DC 2.0 A, max. 30.0 W 20.0 V/DC 1.5 A, max. 30.0 W PPS: 3.3 – 11.0 V/DC 3.0 A, max. 30.0 W 3.3 – 16.0 V/DC 2.0 A, max. 30.0 W
Average efficiency:	90.09%
Efficiency at low load (10%):	81.22%
Power consumption at no load:	<0.1 W
Dimensions:	35.92 x 68.2 x 32.2 mm
Weight:	48.5 g
Packing unit:	2pcs

### Product data

Colour	Article no	EAN
white	7803032	4 034303 034055

## What is GaN?



GaN adapters are a new type of power adapter that have many advantages compared to conventional, silicon-based adapters. GaN stands for Gallium Nitride, a material with a higher power density and efficiency. The use of GaN enables smaller power adapters that can also handle higher voltages and currents and even produce less heat.

This makes our power adapters with **GaN** technology **smaller, faster** and above all, more **energy efficient!**