



# GaN 30 W POWER ADAPTER SET

+ USB-C to USB-C Charging / Data Cable



## Technical details

### Power Adapter W30C GaN:

Colour, surface:	white, plastic
Input connector:	EU connector
Input voltage:	100 - 240 V
Input alternating current frequency:	50 / 60 Hz
Connections:	USB-C
Output:	supports (downwards compatible) PD 3.0, PPS and QC 4.0 5.0 V/DC 3.0 A, max. 15.0 W 9.0 V/DC 3.0 A, max. 27.0 W 12.0 V/DC 2.5 A, max. 30.0 W 15.0 V/DC 2.0 A, max. 30.0 W 20.0 V/DC 1.5 A, max. 30.0 W PPS: 3.3 – 11.0 V/DC 3.0 A, max. 30.0 W 3.3 – 16.0 V/DC 2.0 A, max. 30.0 W
Average efficiency:	90.09%
Efficiency at low load (10%):	81.22%
Power consumption at no load:	<0.1 W
Dimensions, weight:	35.92 x 68.2 x 32.2 mm, 48.5 g

### USB-Cable C315C:

Colour:	white
Material:	nylon and aluminium
Connectors:	connector 1: USB-C connector 2: USB-C
Data transmission speed:	480 Mbps
max. voltage:	20.0 V
max. current strength:	3.0 A
max. performance:	60.0 W
Fast Charging:	supports fast charging (PD 3.0 + QC 4.0) up to 60.0 W
Special features:	reinforced kink protection between USB connector and cable
Cable length:	1.5 m
Weight:	40.0 g

## Product data

Colour	Article no	EAN	Packing unit
white	7803042	4 034303 034086	2 pcs