

Avide (Triton-O) Bulkhead Lamp Oval IP65 20W NW 4000K White 100lm/W

Product code: ABBHL-O-20W-NW-HL
Brand link:
ID: AB-190518
Company name: Bramcke Hungary Kft.
Company address: Kishatár utca 17., 4031 Debrecen

QR code:
Date of issue: 2024-03-11
Page: 1/2

SPECIFICATIONS

EAN code: 5999097950549
Warranty:
Color: White
Material: PC+ABS
Working temperature: -20 -+40°C
Packaging: 1/b 12/c 384/p
Certifications:

TECHNICAL DETAILS

Wattage: 20W
Voltage: 220-240V
Beam angle: 120°
Dimmability: Yes
Lumen output: 2 000lm
Color temperature: 4 000K
Lifetime: 25 000h
Energy class:
Type of LED: SMD2835
CRI: 80
IP standard: IP65

BOX PICTURE



Avide (Triton-O) Bulkhead Lamp Oval IP65 20W NW 4000K White 100lm/W

Product code:	ABBHL-O-20W-NW-HL	QR code:	
Brand link:		Date of issue:	2024-03-11
ID:	AB-190518		
Company name:	Bramcke Hungary Kft.		
Company address:	Kishatár utca 17., 4031 Debrecen	Page:	2/2

PRODUCT SIZE

Width:	145mm
Height:	
Depth:	270mm

CARDBOARD BOX

EAN:	5999097950549
Packaging:	1/b 12/c 384/p
Dimensions:	
Net weight:	401g
Gross weight:	506g

CARTON

EAN:	5999097950556
Packaging:	1/b 12/c 384/p
Dimensions:	
Net weight:	4.812kg
Gross weight:	6.072kg

PALLET EXAMPLE

Height:	
Width:	120cm (std Euro pallet)
Mepth:	80cm (std Euro pallet)
Cartons per pallet:	32carton/pallet
Cartons per row:	
Net weight:	153.984kg
Gross weight:	194.304kg

PRODUCT PICTURE



PRODUCT OUTLINE