

Avide (Triton-R) Bulkhead Lamp Round IP65 20W NW 4000K White 100lm/W

Product code: ABBHL-R-20W-NW-HL
Brand link:
ID: AB-190518
Company name: Bramcke Hungary Kft.
Company address: Kishatár utca 17., 4031 Debrecen

QR code:

Date of issue: 2024-03-11

Page: 1/2

SPECIFICATIONS

EAN code: 5999097950563
Warranty:
Color: White
Material: PC+ABS
Working temperature: -20 -+40°C
Packaging: 1/b 12/c 216/p
Certifications:

TECHNICAL DETAILS

Wattage: 20W
Voltage: 220-240V
Beam angle: 120°
Dimmability: Yes
Lumen output: 2 000lm
Color temperature: 4 000K
Lifetime: 25 000h
Energy class:
Type of LED: SMD2835
CRI: 80
IP standard: IP65

BOX PICTURE



Avide (Triton-R) Bulkhead Lamp Round IP65 20W NW 4000K White 100lm/W

Product code: ABBHL-R-20W-NW-HL
Brand link:
ID: AB-190518
Company name: Bramcke Hungary Kft.
Company address: Kishatár utca 17., 4031 Debrecen

QR code:
Date of issue: 2024-03-11
Page: 2/2

PRODUCT SIZE

Width: 220mm
Height:
Depth: 78mm

CARDBOARD BOX

EAN: 5999097950563
Packaging: 1/b 12/c 216/p
Dimensions:
Net weight: 401g
Gross weight: 506g

CARTON

EAN: 5999097950570
Packaging: 1/b 12/c 216/p
Dimensions:
Net weight: 4.812kg
Gross weight: 6.072kg

PALLET EXAMPLE

Height:
Width: 120cm (std Euro pallet)
Mepth: 80cm (std Euro pallet)
Cartons per pallet: 18carton/pallet
Cartons per row:
Net weight: 86.616kg
Gross weight: 109.296kg

PRODUCT PICTURE



PRODUCT OUTLINE