



Power Strip X CPSX-T1-T3

1x powerCON TRUE1 IN – 3x powerCON® TRUE1® TOP
OUT- Indoor (IP20)

Power Strip Xtreme (X) is a compact distribution solution for mobile applications. This distribution box is ideally suited for Indoor applications with restricted space / height and harsh usage conditions, for example in theaters, exhibition or similar applications. It also offers a very attractive price point.

Features & Benefits

- Extreme robust and safe EASYLEN® housing with leather grain texture
- Highly reliable NEUTRIK® powerCON® TRUE1® TOP recepticals for In, Out and Daisy chaining
- Flame retardant (UL94-V2) and non-conductive housing material
- High mechanical protection (high IK)
- Light weight, compact and stackable housing design
- Versatile mounting options
- Attractive price point

Market & Applications

- Markets: Professional video wall / lighting / audio
- Mobile application: Festivals, live events, exhibitions / trade shows
- Semi-permanent applications: Theaters, studios

Ordering information

Article name	Details	Order code
CPSX-T1-T3	IN: 1 x powerCON® TRUE1® TOP OUT: 3 x powerCON® TRUE1® TOP Indoor (IP20)	1035599

Technical Information

Product

Input device	1x powerCON®TRUE1®TOP
Output device	3x powerCON®TRUE1®TOP
Daisy chaining	1x powerCON®TRUE1®TOP

Electrical

Contact resistance / protection class	Protection class II
Dielectric strength	0.5 kV / mm
Rated voltage	16A (USA: 20A)
Rated Current	16A (USA: 20A)
Number of electrical contacts	2 + PE
Phases	single-phase

Mechanical

Lifetime	> 5000 Mating cycles per connector
Dimensions	220 x 91.2 x 77 mm
Conductor cross section	2.08 mm ²
Weight	0.55 kg
Mounting options	Truss clip, mounting wholes for pegging or suspension

Material

Housing	Easylen
Color	black

Environmental

Standards compatibility	UL94-V2
Protection class	IP20
Temperature range	-25 °C bis +70°C