

Power Strip XO CPVT3RD

Power Strip Xtreme Outdoor. 1x powerCON TRUE1 IN –
3x powerCON® TRUE1® TOP OUT



Power Strip Xtreme Outdoor (XO) is a compact distribution solution for mobile outdoor applications. Rugged EASYLEN® housing is ideally suited for outdoor usage and demanding applications under harsh conditions. 1x powerCON® TRUE1® TOP In and up to 6x powerCON® TRUE1® TOP Out.

Features & Benefits

- Highly reliable NEUTRIK® powerCON® TRUE1® TOP recepticals for In, Out and Daisy chaining
- Flame retardant (UL94-V2) and non-conductive housing material
- High outdoor protection (IP65, IK, ..)
- Light weight, compact and stackable housing design
- Versatile mounting options

Market & Applications

- Markets: Professional video wall / lighting / audio
- Mobile application: Festivals, live events
- Semi-permanent applications: Theaters, studios

Article Variations

Article name	Details	Order code
CPVT3RD	IN: 1 x powerCON® TRUE1® TOP - OUT: 3 x powerCON® TRUE1® TOP	1027452

Technical Information

Product

Input device	1x powerCON®TRUE1®TOP with self-closing caps
Output device	3x powerCON®TRUE1®TOP with self-closing caps
Daisy chaining	1x powerCON®TRUE1®TOP with self-closing caps

Electrical

Contact resistance / protection class	Protection class II
Dielectric strength	0.5 kV / mm
Rated voltage	250V AC
Rated Current	16A (USA: 20A)
Number of electrical contacts	2 + PE
Phases	single-phase

Mechanical

Lifetime	> 5000 Mating cycles per connector
Dimensions	220 x 91.2 x 77 mm
Conductor cross section	2.08 mm ²
Weight	0.65 kg
Mounting options	Truss clip, mounting wholes for pegging or suspension

Material

Housing	Easylen
Color	black

Environmental

Standards compatibility	UL94-V2
Protection class	IP65
Temperature range	-25 °C bis +70°C