



Power Strip XO CCV5RD-6T1-C

1x CEE16A IN - 6x powerCON TRUE1® TOP OUT

Power Strip Xtreme Outdoor (XO) is a compact distribution solution for mobile outdoor applications. Rugged EASYLEN® housing is ideally suited for outdoor usage and demanding applications under harsh conditions. 1x CEE16A In and up to 6x powerCON® TRUE1® TOP Out.

Features & Benefits

- Extreme robust and safe EASYLEN® housing with leather grain texture
- Mains receptacles CEE16A In & daisy chaining and highly reliable NEUTRIK® powerCON® TRUE1® TOP Out
- Flame retardant (UL94-V2) and non-conductive housing material
- High outdoor protection (IP65, IK, ..)
- Light weight, compact and stackable housing design
- Versatile mounting options

Applications and markets

- Main markets: Professional video walls, event lighting, pro-audio
- Mobile application: Festivals, live events
- Semi-permanent applications: Theaters, studios

Ordering Information

Article name	Details	Order code
CCV5RD-6T1-C	IN: 1xCEE16A - OUT: 6x powerCON® TRUE1® TOP	1027454

Technical Information

Product

Input device	1 x CEE16-5
Output device	6 x powerCON® TRUE1® TOP
Daisy chaining	none

Electrical

Contact resistance / protection class	Protection class II
Dielectric strength	0.5 kV / mm
Rated voltage	400 V AC
Rated Current	16 A
Number of electrical contacts	4 + PE
Phases	multi-phase (3+N+PE)

Mechanical

Dimensions	489.6 x 92 x 117.2mm
Conductor cross section	2.5 mm ²
Weight	2.1 kg
Mounting options	Truss clip, truss clamp, mounting wholes for pegging or suspension

Material

Housing	Easylen
Color	black

Environmental

Standards compatibility accotding to UL94	V2
Protection class	IP65
Temperature range	-25 °C bis +40°C