



CCV5RD

Outdoor Power Strip XO with 6 powerCON® TRUE1® TOP out sockets in rugged EASYLEN® housing for harsh environment. Equipped with 3-phase input connector for higher power consumption. Ideally suited for outdoor usage and under harsh conditions.

Features & Benefits

- Extreme robust and safe EASYLEN® housing, flame retardant material (UL94 V2)
- Mounting options / truss clip / truss clamp
- Self closing caps
- Light weight and compact design
- IP 65 rated / IK 10+ rated (impact resistant)
- Reliable NEUTRIK® powerCON® TRUE1® TOP recepticals
- Daisy chaining

Article Variations

| Article name | Details | Order code |
|---------------|---|------------|
| CCV5RD-6T1-C | 6x powerCON® TRUE1® TOP with CEE16-5 In IP65 Power Strip XO | 1027454 |
| CCV5RD-6T1-2C | 6x powerCON® TRUE1® TOP with CEE16-5 In and Out IP65 Power Strip XO | 1027455 |

Technical Information

| Product | |
|---------------|--|
| Input device | CEE16-5 CCV5RD-6T1-C |
| | CEE16-5 CCV5RD-6T1-2C |
| Output device | 6x powerCON® TRUE1® TOP CCV5RD-6T1-C |
| | 6x powerCON® TRUE1® TOP with CEE16-5 CCV5RD-6T1-2C |
| Design | Mobile / portable |

| Electrical | |
|---------------------------------------|----------------------|
| Contact resistance / protection class | Protection class II |
| Dielectric strength | 0,5 kV / mm |
| Rated voltage | 250V AC |
| Rated Current | 16A (USA: 20A) |
| Number of electrical contacts | 4 + PE |
| Phases | multi-phase (3+N+PE) |

| Mechanical | |
|-------------------------|------------------------------------|
| Dimensions | 489,6 x 92 x 117,2mm CCV5RD-6T1-C |
| | 528,6 x 92 x 117,2mm CCV5RD-6T1-2C |
| Conductor cross section | 2,5mm ² |

| Material | |
|----------|---------|
| Housing | Easylen |
| Color | black |

Environmental

| | |
|--------------------------------|------------------|
| Standards compatibility | UL94-V2 |
| Protection class | IP65 |
| Temperature range | -25 °C to +80 °C |

Mobile cable

| | |
|---------------|---------------------|
| Weight | 1,9kg CCV5RD-6T1-C |
| | 2,1kg CCV5RD-6T1-2C |